

# Data sheet

## 28119.7 PC-TDMO-03 4X16 WH



Wire and cable markers, Length: 16 mm, Width: 4 mm, Colour: White

RAL: 9010

### Business data

|                                            |                        |
|--------------------------------------------|------------------------|
| Article number                             | 28119.7                |
| Article name                               | PC-TDMO-03 4X16 WH     |
| GTIN (EAN)                                 | 4044211212124          |
| Packaging unit                             | 560                    |
| Quantity unit                              | PC                     |
| Number of markers per card                 | 40 ST                  |
| Weight per piece (not including packaging) | 0.4 g                  |
| Weight per piece (including packaging)     | 0.4 g                  |
| Unit of weight                             | G                      |
| Customs number                             | 39269097               |
| Country of origin                          | IT                     |
| Prio-Article                               | 28119.7                |
| Product description                        | Cable and wire markers |

### Technical data

#### Dimensions

|        |       |
|--------|-------|
| Length | 16 mm |
|--------|-------|

|       |      |
|-------|------|
| Width | 4 mm |
|-------|------|

#### Connection data

|                          |                   |
|--------------------------|-------------------|
| Wire cross-section, min. | 4 mm <sup>2</sup> |
|--------------------------|-------------------|

|                          |                   |
|--------------------------|-------------------|
| Wire cross-section, max. | 6 mm <sup>2</sup> |
|--------------------------|-------------------|

|                                    |      |
|------------------------------------|------|
| Outer diameter of insulation, min. | 4 mm |
|------------------------------------|------|

|                                   |        |
|-----------------------------------|--------|
| Max. outer diameter of insulation | 4.6 mm |
|-----------------------------------|--------|

#### Materials

|                 |               |
|-----------------|---------------|
| Marker material | Polycarbonate |
|-----------------|---------------|

|                          |     |
|--------------------------|-----|
| Flammability class UL 94 | V-0 |
|--------------------------|-----|

|                           |        |
|---------------------------|--------|
| Working temperature, min. | -40 °C |
|---------------------------|--------|

|                           |        |
|---------------------------|--------|
| Working temperature, max. | 130 °C |
|---------------------------|--------|

|              |   |
|--------------|---|
| Halogen-free | ✓ |
|--------------|---|

|               |   |
|---------------|---|
| Silicone-free | ✓ |
|---------------|---|

#### Further technical data

|               |     |
|---------------|-----|
| Software code | 130 |
|---------------|-----|

#### Environmental Product Compliance

|                                |    |
|--------------------------------|----|
| REACH Candidate Substance Note | No |
|--------------------------------|----|

---

Media

---

### Accessories

#### Printer



Thermal transfer printer TTPCard including a power cord, USB cable, dust cover, black thermal transfer film (28010.4), three inlays: CCI-PC-SB 5x5 (28020.0), CCI-PC-CPM-10/BSTR (28027.0), CCI-PC/PVC/PVCF (28041.0), CONTASign PRO software in 16 languages (German, English, French, Italian, Dutch, Spanish, Portuguese, Czech, Polish, Bulgarian, Romanian, Slovenian, Turkish, Chinese, Japanese, Russian) for Windows versions 7, 8, 10. (available for download)

| Article number | Article name | GTIN (EAN)    | Packaging unit |
|----------------|--------------|---------------|----------------|
| <u>28000.0</u> | TTPCard Set  | 4044211207397 | 1 ST           |

#### Inlays

##### Printer inlay

| Article number | Article name | GTIN (EAN)    | Packaging unit |
|----------------|--------------|---------------|----------------|
| <u>28022.0</u> | CCI-PC-TDMO  | 4044211207908 | 1 ST           |