

Specification Sheet

Part Number: 156-02251

Patented retention design on clip features inverted retaining legs, narrow opening and circular retainer to prevent inadvertent disengagement. Controlled flex and angled entry promote easy installation.

Independent rotation allows for adjustable routing orientation.

Cable tie accommodates wide range of secondary bundle sizes.



MOC Clip, 7 mm Transverse, Assembled to T50SVC Swivel Tie, PA66HIRHSUV, Black, 2000/ctn

Article Number	156-02251
----------------	-----------

Type	T50SVC MOC7M180
------	-----------------

Color	Black (BK)
-------	------------

Quantity Per	carton
--------------	--------

Product Description	The MOC 180 to Swivel Tie is a rotatable routing clip coupled to a cable tie that keeps two routings secured and separated. Tie provides additional security against axial slip by clamping around solid tube, pipe or harness. The clip's orientation allows the second routing to be assembled in the direction of the first routing. The swivel coupler allows the two routings to rotate independently of each other.
---------------------	---

Short Description	MOC Clip, 7 mm Transverse, Assembled to T50SVC Swivel Tie, PA66HIRHSUV, Black, 2000/ctn
-------------------	---

Global Part Name	T50SVCMOC7M180-PA66HIRHSUV-BK
------------------	-------------------------------

Minimum Tensile Strength (Imperial)	50.0
-------------------------------------	------

Minimum Tensile Strength (Metric)	225
-----------------------------------	-----

Length L (Imperial)	0.46
---------------------	------

Length L (Metric)	11.6
-------------------	------

Fixation Method	Omega Clips
-----------------	-------------

Identification Plate Position	none
-------------------------------	------

Bundle Diameter Min (Imperial)	0.24
--------------------------------	------

Bundle Diameter Min (Metric)	6.0
------------------------------	-----

Bundle Diameter Max (Imperial)	0.31
--------------------------------	------

Bundle Diameter Max (Metric)	8.0
------------------------------	-----

Height H (Imperial)	1.14
---------------------	------

Height H (Metric)	28.9
-------------------	------

Depth D (Imperial)	0.39
--------------------	------

Depth D (Metric)	10.0
------------------	------

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Operating Temperature	-40°F to +230°F (-40°C to +110°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Package Quantity (Imperial)	2000
Package Quantity (Metric)	2000
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

