



TE Internal #: 1-2273008-2
M8 Pigtail Cable Assembly, 3 Position, 3 m, Sensor/Actuator, Code
A, M8 Plug, Single Ended, Plastic
[View on TE.com >](#)

Cable Assemblies > Copper Cable Assemblies > M8/M12 Cable Assemblies > M8 Connector: Pigtail Cable, Right Angle



M8/M12 Application Type: **Sensor/Actuator**
Number of Positions: **3**
Connector & Keying Code: **A**
Connector Type (End A): **M8 Plug**
Cable Assembly Type: **M8 Pigtail**

[All M8 Connector: Pigtail Cable, Right Angle \(16\)](#)

Features

Product Type Features

Connector Type (End A)	M8 Plug
Cable Assembly Type	M8 Pigtail

Configuration Features

Number of Positions	3
---------------------	---

Electrical Characteristics

Operating Voltage	60 VAC
-------------------	--------

Body Features

Cable Color	Black
Connector Color (End A)	Black
Jacket Material	PVC
Wire Color (Base)	Brown, Blue, Black
Connector & Keying Code	A

Contact Features

Contact Current Rating (Max)	4 A
------------------------------	-----

Mechanical Attachment

Thread Size	M8
Connector Orientation (End A)	Right Angle



Housing Features

Housing Material	Plastic
------------------	---------

Dimensions

Outside Cable Diameter	4.5 mm[.177 in]
Wire Size	.326 mm ²

Usage Conditions

Operating Temperature Range	-30 – 80 °C[-22 – 176 °F]
-----------------------------	---------------------------

Operation/Application

M8/M12 Application Type	Sensor/Actuator
Shielded	No

Packaging Features

Packaging Quantity	25
Packaging Method	Box

Other

Field Serviceable	Yes
Cable Assembly Length	3 m
Cable Assembly Configuration	Single Ended

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as



EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # T4051410003-004

M8 CABLE RA FEMALE 3M 3P PVC CABLE

Customers Also Bought

TE Part #1-2273001-1

M8 x 1.0 straight socket Pigtail

TE Part #T4141012041-000

M12,REAR MOUNTING,FEMALE,A CODE,4P

TE Part #T4062113003-005

RPC-M8-3MS-5.0SH-M8-3FS-PVC

TE Part #T4071017031-001

M8.FMLE.PNLREAR.3POS.STR WIRE

TE Part #T4162124004-002

RPC-M12-4MS-1.0SH-M12-4FR-PUR

TE Part #T4110011041-000

M12 F, 4P GOLD A_CODE S SHIELDED PG7

TE Part #34150

PG R 22-16 COMM 22-18 MIL 1/4

TE Part #1838893-2

M12 Mtl MALE PNL CONN. SlDr Rear (Hex)

TE Part #36151

PIDG R 22-16 COMM 22-18 MIL 6

TE Part #NB18742001

RNF-100-1/16-BK-STK



Documents

Product Drawings

M8 x 1.0 Angled plug Pigtail

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-2273008-2_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-2273008-2_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-2273008-2_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

M8 / M12 Connector System Catalog

English

M8 / M12 Connector System Catalog

Japanese

Product Specifications

Product Specification

English