

DMS-59 to Dual VGA Splitter Y Cable (M to 2xF),
1 ft. (0.31 m)

MODEL NUMBER: P574-001



Highlights

- Attach two VGA enabled monitors to your DMS59 Graphics card
- Superior molded connectors for long life use

Package Includes

DMS59 to (2) VGA Female Splitter Cable - 1-ft. (0.31 m)

Features

- LFH59 (DMS59) to 2 x VGA Female, 1-ft. (0.31 m)
- Compatible with most DMS-59 video cards including nVidia, Matrox, HP, PNY, and ATI
- Rugged molded construction and gold plated contacts

Specifications

OVERVIEW	
UPC Code	037332145987
Product Type	Splitter
Technology	VGA/SVGA
Host Connector	DMS59 (MALE)
Cable Type	Passive
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	1
Cable Length (m)	0.30
Cable Length (in.)	12
Shipping Dimensions (hwd / in.)	11.00 x 7.00 x 0.50

Shipping Dimensions (hwd / cm)	27.94 x 17.78 x 1.27
Shipping Weight (lbs.)	0.30
Shipping Weight (kg)	0.14
CONNECTIONS	
Side A - Connector 1	DMS59 (MALE)
Side B - Connector 1	(2) HD15 (FEMALE)
Latching or Gripping Connector	No
Input x Output	1 x 2
Daisy-chainable / Cascadable	No
FEATURES & SPECIFICATIONS	
MST Support	No
IP68 Rated	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty