

Desktop Computer AC Power Cable, NEMA 5-15P to C13 - 10A, 125V, 18 AWG, 15 ft. (4.57 m), Black

MODEL NUMBER: P006-015











Computer power cable allows you to connect your PC, printer or monitor into a surge protector, PDU or UPS with a NEMA 5-15R outlet.

Features

Desktop Computer Power Cord Connects PCs, Printers, Monitors and Other EquipmentThis computer power supply cable is designed for home/office desktop computer applications. You can use it to connect a computer, monitor, printer, scanner or other device with a C14 power inlet to an AC wall outlet, surge protector, UPS system or PDU. The 15-ft. (4.57 m) length allows you great flexibility in placing equipment with respect to the power outlet.

Highlights

- Recommended for powering computers, printers and other home/office peripherals
- 15-ft. (4.57 m) length allows great flexibility in placing devices in relationship to AC outlet
- NEMA 5-15P to C13 extension cord is ideal replacement for worn-out or missing cable

Applications

- Connect devices like computers, printers and monitors to a PDU up to 15-ft. (4.57 m) away in your workstation
- Extend an existing power connection up to 15-ft. (4.57 m) to more easily place a device or reach a power source
- Provide a high-quality replacement for a worn-out or missing power cord

Package Includes

 P006-015 NEMA 5-15P to C13 Computer Power Cable, 15-ft. (4.57 m), Black

Specifications

OVERVIEW		
UPC Code	037332176806	
Device Compatibility	Computer; Monitor/HDTV; Printer; Server; UPS; PDU	
Country/Region	North America	
INPUT		
Maximum Input Amps	10	
Voltage Compatibility (VAC)	125	
PHYSICAL		
Color	Black	
Cable Jacket Color	Black	
Cable Jacket Material	PVC	



Cable Jacket Rating	VW-1	
Power Cord Jacket Type	SJT	
Cable Outer Diameter (OD)	7.8mm	
Number of Conductors	3	
Wire Gauge (AWG)	18	
Wire Gauge (OD - mm²)	0.82	
Cable Length (ft.)	15	
Cable Length (m)	4.57	
Shipping Dimensions (hwd / in.)	12.80 x 8.86 x 0.50	
Shipping Dimensions (hwd / cm)	32.51 x 22.50 x 1.27	
Shipping Weight (lbs.)	0.97	
Shipping Weight (kg)	0.44	
ENVIRONMENTAL		
Operating Temperature Range	-4° to 140°F (-20° to 60°C)	
Storage Temperature Range	-4° to 140°F (-20° to 60°C)	
Relative Humidity	10% to 85% RH	
CONNECTIONS		
Side A - Connector 1	NEMA 5-15P	
Side B - Connector 1	IEC-320-C13	
FEATURES & SPECIFICATIONS		
Antibacterial	No	
Angled Plug	No No	
High Voltage	No	
Locking Plug	No	
Coiled Power Cord	No	
STANDARDS & COMPLIANCE		
Product Certifications	cUL Listed; UL Listed	
Product Compliance	RoHS	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	







© 2023 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.