

Specification Sheet

Part Number: 133-03178



Inverted retaining legs and narrow opening prevent inadvertent disengagement
Controlled flex and angled entry promote easy installation
Robust arrowhead design provides low insertion effort yet delivers exceptional retention strength in a 65 mm hole in panels from 12 to 16 mm

Tube and Pipe Clip with 6.5mm Arrowhead, 4.7-5.1mm Diameter, PA66HIRHS, Black, 4000/ctn

Article Number	133-03178
Type	PC5AH6.5
Color	Black (BK)
Quantity Per	carton
Product Description	This clip features a modular design that can be used individually or lined together to secure multiple pipes or hoses.
Short Description	Tube and Pipe Clip with 6.5mm Arrowhead, 4.7-5.1mm Diameter, PA66HIRHS, Black, 4000/ctn
Global Part Name	PC5AH6.5-PA66HIRHSUV-BK

Length L (Imperial)	0.67
Length L (Metric)	17.0
Fixation Method	Arrowhead
Width W (Metric)	10.0
Height H (Imperial)	0.86
Height H (Metric)	21.5
Panel Thickness Min (Imperial)	0.05
Panel Thickness Max (Imperial)	0.06
Panel Thickness Min (Metric)	1.2
Panel Thickness Max (Metric)	1.6
Mounting Hole Diameter D (Metric)	6.1 - 6.9 mm 6.35 mm (hexagonal)
Disc Diameter (Metric)	17.0
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB

UV Resistant (Yes/No)	Yes
Operating Temperature	-40°F to +230°F (-40°C to +110°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Package Quantity (Imperial)	4000
Package Quantity (Metric)	4000
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).