

Specification Sheet

Part Number: 151-02061



Angled channel allows specific guidance around corners or obstructions.
U-Shape channel provides three sides of protection for wire or bundle.
High-quality polypropylene material with high heat resistance.
Protects against abrasion and other environmental factors.

Mini-Channel, 60mm Long, 90 Degree, 22.5mm Radius Angle, PPT20, Black, 1000/ctn

Article Number	151-02061
Type	90RADMINICHNL
Color	Black (BK)
Quantity Per	carton
Product Description	The mini-channel family allows a cost effective routing solution that provides protection and configurable routing. Pieces are modular and interchangeable, providing high levels of customization. Mini channels replace engineered channels that are costly to design and develop.
Short Description	Mini-Channel, 60mm Long, 90 Degree, 22.5mm Radius Angle, PPT20, Black, 1000/ctn
Global Part Name	90RADMINICHNL-PPTD20-BK

Length L (Imperial)	2.34
Length L (Metric)	59.5
Width W (Metric)	59.5
Height H (Metric)	1.75
Mounting Hole Diameter D (Imperial)	0.246 - 0.265
Mounting Hole Diameter D (Metric)	6.25 - 6.75 mm
Mounting Hole Diameter D Max (Metric)	6.75
Material	Polypropylene 20% Talkum (PPTD20)
Material Shortcut	PPTD20
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +149°F (-40°C to +65°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	1000

Package Quantity (Metric)	1000
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)