




- SPECIFICATIONS**
1. Current Rating: 3A AC, DC
 2. Voltage Rating: 250V AC, DC
 3. Temperature Range: -25°C~ +85°C
 4. Contact Resistance: 20mΩ Max
 5. Insulation Resistance: 1000mΩ Min
 6. Withstanding Voltage: 1000V AC/minute
 7. Material: Wafer LCP UL94-VO
Pin Brass Tin-plated

Circuit	Part NO.	Dimensions mm		
		A	B	C
2	XD-XH-2AWT-XX	2.50	7.50	10.00
3	XD-XH-3AWT-XX	5.00	10.00	12.50
4	XD-XH-4AWT-XX	7.50	12.50	15.00
5	XD-XH-5AWT-XX	10.00	15.00	17.50
6	XD-XH-6AWT-XX	12.50	17.50	20.00
7	XD-XH-7AWT-XX	15.00	20.00	22.50
8	XD-XH-8AWT-XX	17.50	22.50	25.00
9	XD-XH-9AWT-XX	20.00	25.00	27.50
10	XD-XH-10AWT-XX	22.50	27.50	30.00
11	XD-XH-11AWT-XX	25.00	30.00	32.50
12	XD-XH-12AWT-XX	27.50	32.50	35.00
13	XD-XH-13AWT-XX	30.00	35.00	37.50
14	XD-XH-14AWT-XX	32.50	37.50	40.00
15	XD-XH-15AWT-XX	35.00	40.00	42.50
16	XD-XH-16AWT-XX	37.50	42.50	45.00



GENERAL TOLERANCE			制图 DRAWING	01		
			审核 CHECK			
			批准 APPROVAL			
1	初版发行		比例 SCALE			
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	投影 Projection		材料 MATERIAL	
			深圳讯答科技有限公司 ShenzhenXunDaTechnology Co.,Ltd		产品名称 TITLE	XH (2.50) 单排 卧贴
					版本 REV.	A
					产品料号 PART NO.	XD-XH-NAWT-XX
					单位 UNITS	mm
					页次 SHEET	1/1