

Power Extension Cord, Right-Angle NEMA 5-15P to NEMA 5-15R - 13A, 120V, 16 AWG, 15 ft. (4.6 m), Black

MODEL NUMBER: P022-015-13A15D



13-amp extension cord connects two devices with 5-15P/5-15R power connectors or extends your existing power connection.

Features

15-Foot Extension Cord Connects Printers, Servers and Other Equipment

This power extension cable is designed for small data center or office workstation applications that do not require a heavy-gauge connection. With a right-angle NEMA 5-15P plug on one end and a NEMA 5-15R receptacle on the other, this cord can be used to power a printer or monitor; attach a rack server to a UPS system or PDU; or extend an existing connection up to 15 feet (4.6 meters). The 15-foot length allows you great flexibility in placing equipment with respect to the power outlet.

Right-Angle Plug Makes Connecting in Tight Spaces Easier

The space-saving right-angle NEMA 5-15P connector is easy to install in confined spaces, such as behind your computer desk or workstation. The right-angle construction also relieves strain on the cable and connector and prevents the cable from bending awkwardly.

Specifications

OVERVIEW	
UPC Code	037332275240
Device Compatibility	Computer; Monitor/HDTV; Printer; Server; UPS; PDU
Country/Region	North America
INPUT	
Maximum Input Amps	13
Voltage Compatibility (VAC)	125

Highlights

- Recommended for powering computers, monitors and other essential peripherals
- Ideal for home/office applications, small server rooms and data centers
- Right-angle plug allows easier connection in confined or hard-to-reach spaces
- Adds 15 ft. to your existing connection to provide more flexibility in placing devices
- Ideal replacement for worn-out or missing 15 ft. extension cord

Package Includes

P022-015-13A15D Power Extension Cord, Right-Angle NEMA 5-15P to NEMA 5-15R, 15 ft. (4.6 m), Black

PHYSICAL	
Plug Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	FT2
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	8.3 mm
Number of Conductors	3
Wire Gauge (AWG)	16
Wire Gauge (OD - mm ²)	1.31
Cable Length (ft.)	15
Cable Length (m)	4.57
Shipping Dimensions (hwd / in.)	14.17 x 11.80 x 0.50
Shipping Dimensions (hwd / cm)	35.99 x 29.97 x 1.27
Shipping Weight (lbs.)	1.05
Shipping Weight (kg)	0.48
ENVIRONMENTAL	
Operating Temperature Range	-4° to 140°F (-20° to 60°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Operating Humidity Range	20% TO 80% RH, Non-Condensing
Storage Humidity Range	20% to 80% RH, Non-Condensing
CONNECTIONS	
Side A - Connector 1	NEMA 5-15P - RIGHT ANGLE
Side B - Connector 1	NEMA 5-15R
FEATURES & SPECIFICATIONS	
Antibacterial	No
Angled Plug	Yes
High Voltage	No
Locking Plug	No
Coiled Power Cord	No
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL Listed

Product Compliance	RoHS; REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty