

## ATGBICS MFS4R12CB-003 NVIDIA Mellanox Compatible Active Optical Cable 40G QSFP+ (3m)

**Brand :** ATGBICS

**Product code:** MFS4R12CB-003-C

**Product name :** MFS4R12CB-003 NVIDIA Mellanox Compatible Active Optical Cable 40G QSFP+ (3m)

MFS4R12CB-003 NVIDIA Mellanox Compatible Active Optical Cable 40G QSFP+ (3m)

**ATGBICS MFS4R12CB-003 NVIDIA Mellanox Compatible Active Optical Cable 40G QSFP+ (3m):**

ATGBICS MFS4R12CB-003 compatible 40GBase QSFP+ to QSFP+ active optical cable operates at a wavelength of 850nm over multimode fibre with a cable length of 3m. It is suitable for short reach connection between two QSFP+ ports in 40G interconnecting networking applications. Our product meets the specification of Mellanox MFS4R12CB-003= and we proudly offer a compatibility guarantee and lifetime warranty. Our rigorously tested products record a unique traceable serial number and are fully compliant with all MSA Standards and protocols including; 40G InfiniBand 8x DDR, 4x QDR, 40Gigabit Ethernet IEEE802.3ba, Fibre Channel, MSA QSFP+ SFF-8436 compliant.

ATGBICS MFS4R12CB-003 NVIDIA Mellanox Compatible Active Optical Cable 40G QSFP+ (3m). Cable length: 3 m, Connector 1: QSFP+, Connector 2: QSFP+, Data transfer rate: 40000 Mbit/s



Features		Features	
Product colour *	Orange	Country of origin	United Kingdom
Cable length *	3 m	<b>Operational conditions</b>	
Connector 1 *	QSFP+	Operating temperature (T-T)	0 - 70 °C
Connector 2 *	QSFP+	Storage temperature (T-T)	-40 - 80 °C
Connector 1 gender *	Male	Operating relative humidity (H-H)	10 - 90%
Connector 2 gender *	Male	Storage relative humidity (H-H)	10 - 85%
Jacket material	Optical fiber non-conductive plenum (OFNP)	<b>Packaging data</b>	
Ethernet interface type	40 Gigabit Ethernet	Quantity per pack	1 pc(s)
Networking standards	IEEE 802.3ba	<b>Technical details</b>	
AWG wire size	30	Sustainability compliance	✓
Data transfer rate	40000 Mbit/s	Sustainability certificates	RoHS
Plug and Play	✓	Doesn't contain	Lead
Certification	CE, FCC, RoHS		



5056468726995

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 21-SEP-2023. Prints or copies of Information are only valid on the printed Publication date