

## Specification Sheet

Part Number: 558-00377

Pre-printed header striped continuous vinyl rolls come in different header colors, providing a variety of printing options.

The headers can be printed with various ARC FLASH, WARNING And CAUTION headlines to meet OSHA safety standards for identifying electrical panels and equipment.

Signs can be designed in TagPrint Pro labeling software and printed with any HellermannTyton thermal transfer printing system with optional cutter attached.



Adhesive Labels, Solid Color Continuous Roll, Reflective, 1.0" x 250', VL, Red, 250 ft/roll

Article Number

558-00377

Type

HT1RDRF250

Color

Red Reflective (RDRF)

Quantity Per

roll

Product Description

Continuous Vinyl Labels are made with UV-stable materials for long outdoor life. The labels are extruded in the actual color and not colored using surface inks for long-term fade resistance. Vinyl labels are provided in continuous rolls so that the markers can be printed and cut to any length using HellermannTyton thermal transfer printing systems. Good for all surface types except powder coat painted or low surface energy substrates such as polypropylene. Test on these surfaces before approving.

|                           |                                                                                             |
|---------------------------|---------------------------------------------------------------------------------------------|
| Short Description         | Adhesive Labels, Solid Color Continuous Roll, Reflective, 1.0" x 250', VL, Red, 250 ft/roll |
| Global Part Name          | HT1RDRF250-V-RD                                                                             |
| Length L (Imperial)       | 250.0                                                                                       |
| Length L (Metric)         | 76.20                                                                                       |
| Variant                   | 3.2mil, 50lb bleached kraft paper                                                           |
| Width W (Imperial)        | 1.0                                                                                         |
| Width W (Metric)          | 25.4                                                                                        |
| Thickness T (Metric)      | 64.0                                                                                        |
| Width of Liner (Metric)   | 25.40                                                                                       |
| Width of Liner (Imperial) | 1.0                                                                                         |
| Material                  | Vinyl (V)                                                                                   |
| Material Shortcut         | V                                                                                           |
| Adhesive                  | Acrylic                                                                                     |
| Halogen Free              | No                                                                                          |

|                                |                                         |
|--------------------------------|-----------------------------------------|
| UV Resistant (Yes/No)          | Yes                                     |
| Adhesive Operating Temperature | -40°F to +180°F (-40°C to +82°C)        |
| Operating Temperature          | -40°F to +180°F (-40°C to +82°C)        |
| Reach Compliant (Article 33)   | Yes                                     |
| ROHS Compliant                 | Yes                                     |
| Certification/Specification    | NEC2011 NEC2014 NEC2020 NEC2023 NEC2017 |
| Package Quantity (Imperial)    | 250                                     |
| Package Quantity (Metric)      | 76.20                                   |
| Customs Number                 | 3919102055                              |
| Labels per Column              | 1                                       |
| Labels per Row                 | 1                                       |

### About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. ([www.hellermann.tyton.com](http://www.hellermann.tyton.com)).

