


4~20 Pin




SPECIFICATIONS

1. Current Rating: 3A AC, DC
2. Voltage Rating: 250V AC, DC
3. Temperature Range: -25°C~ +85°C
4. Contact Resistance: 10mΩ Max
5. Insulation Resistance: 1000mΩ Min
6. Withstanding Voltage: 1000V AC/minute
7. Material: Housing PA66 UL94-VO

Circuit	Part NO.	Dimensions mm		
		A	B	C
2	XD-XHB-2Y-X	2.50	5.70	3.00
3	XD-XHB-3Y-X	5.00	8.20	4.00
4	XD-XHB-4Y-X	7.50	10.70	5.00
5	XD-XHB-5Y-X	10.00	13.20	7.50
6	XD-XHB-6Y-X	12.50	15.70	10.00
7	XD-XHB-7Y-X	15.00	18.20	
8	XD-XHB-8Y-X	17.50	20.70	
9	XD-XHB-9Y-X	20.00	23.20	
10	XD-XHB-10Y-X	22.50	25.70	
11	XD-XHB-11Y-X	25.00	28.20	
12	XD-XHB-12Y-X	27.50	30.70	
13	XD-XHB-13Y-X	30.00	33.20	12.50
14	XD-XHB-14Y-X	32.50	35.70	
15	XD-XHB-15Y-X	35.00	38.20	
16	XD-XHB-16Y-X	37.50	40.70	
17	XD-XHB-17Y-X	40.00	43.20	
18	XD-XHB-18Y-X	42.50	45.70	
19	XD-XHB-19Y-X	45.00	48.20	
20	XD-XHB-20Y-X	47.50	50.70	

Ordering Information

XD - XHB - N*** - *



GENERAL TOLERANCE			制图 DRAWING	10	深圳讯答科技有限公司 ShenzhenXunDaTechnology Co.,Ltd			
DIM TOL			审核 CHECK					
X.X ±0.30			批准 APPROVAL		产品名称 TITLE	XHB (2.50) 单排带扣孔座	版本 REV.	A
X.XX ±0.20			比例 SCALE	投影 Projection	产品料号 PART NO.	XD-XHB-NY-X	单位 UNITS	mm
X.XXX ±0.10								
1	初版发行							
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE			材料 MATERIAL		页次 SHEET	1/1