

Specification Sheet

Part Number: TELS-SPK2



Spacers provide distance between two bundles.
Continuous strap and separate heads allow for any bundle diameter, eliminating waste.
Smooth strap prevents cable damage.
UV resistant materials contain an inhibitor which prolongs the life of the tie in outdoor environments.

Extended-Length Tie Spacer, PP, Black, 50/pkg

Article Number	111-32000
Type	EL-TY (TELS-SPK2)
Color	Black (BK)
Quantity Per	bag
Product Description	Extended Length Ties provide a high tensile strength strapping system consisting of a continuous strap and separate locking head making it suitable for any bundle diameter, eliminating waste. The smooth strap and specially designed heads with stainless steel pawls provide a strong grip on cables and wires without damage during vibration or in extreme environments. Spacers are available for dual bundle applications.
Short Description	Extended-Length Tie Spacer, PP, Black, 50/pkg

Global Part Name	EL-TY (TELS-SPK2)-PP-BK
------------------	-------------------------

Contents of pkg/kit	50 Spacer
---------------------	-----------

Minimum Tensile Strength (Imperial)	250.0
-------------------------------------	-------

Minimum Tensile Strength (Metric)	1115.0
-----------------------------------	--------

Length L (Imperial)	1.2
---------------------	-----

Length L (Metric)	30.5
-------------------	------

Fixation Method	2 piece
-----------------	---------

Identification Plate Position	none
-------------------------------	------

Releasable Closure	No
--------------------	----

Tie Closure	steel pawl
-------------	------------

Variant	Extended Length
---------	-----------------

Width W (Imperial)	2.1
--------------------	-----

Width W (Metric)	53.3
------------------	------

Height H (Imperial)	0.67
---------------------	------

Height H (Metric)	17.0
-------------------	------

Cable Tie Width Max (Metric)	12.7
------------------------------	------

Material	Polypropylene (PP)
Material Shortcut	PP
Material Head	Polyacetal, UV stabilized (POMUV) with stainless steel pawl (SS)
Flammability	UL 94 HB
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +239°F (-40°C to +115°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	50
Package Quantity (Metric)	50
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

