



- SPECIFICATIONS
- Current Rating: 3A AC, DC
 - Voltage Rating: 250V AC, DC
 - Temperatur Range: -25°C~ +85°C
 - Contact Resistance: 30mΩ Max
 - Insulation Resistance: 1000mΩ Min
 - Withstanding Voltang: 650V AC/minute
 - Material: Wafer Nylon66 UL94-VO
PIN Brass Tin-plated

Circuit	Part NO.	Dimensions mm	
		A	B
2	XD-XHD-2x2AW-X-XX	2.50	7.50
3	XD-XHD-2x3AW-X-XX	5.00	10.00
4	XD-XHD-2x4AW-X-XX	7.50	12.50
5	XD-XHD-2x5AW-X-XX	10.00	15.00
6	XD-XHD-2x6AW-X-XX	12.50	17.50
7	XD-XHD-2x7AW-X-XX	15.00	20.00
8	XD-XHD-2x8AW-X-XX	17.50	22.50
9	XD-XHD-2x9AW-X-XX	20.00	25.00
10	XD-XHD-2x10AW-X-XX	22.50	27.50
11	XD-XHD-2x11AW-X-XX	25.00	30.00
12	XD-XHD-2x12AW-X-XX	27.50	32.50
13	XD-XHD-2x13AW-X-XX	30.00	35.00
14	XD-XHD-2x14AW-X-XX	32.50	37.50
15	XD-XHD-2x15AW-X-XX	35.00	40.00
16	XD-XHD-2x16AW-X-XX	37.50	42.50
17	XD-XHD-2x17AW-X-XX	40.00	45.00
18	XD-XHD-2x18AW-X-XX	42.50	47.50
19	XD-XHD-2x19AW-X-XX	45.00	50.00
20	XD-XHD-2x20AW-X-XX	47.50	52.50

Ordering Information

XD - XHD - N - *** - * - **

Pin	Type	Colour	Contact Plating
	T型插 T型插 AW带针	蓝色 黄色 红色 绿色 白色 黑色 紫色 灰色	Sn Au Ni Ag Cu Pd Pt Cr

GENERAL TOLERANCE			制图 DRAWING	05	深圳讯答科技有限公司 ShenzhenXunDaTechnology Co.,Ltd			
DIM TOL			审核 CHECK					
X.X ±0.30			批准 APPROVAL		产品名称 TITLE	XHD (2.50) 双排 弯针	版本 REV.	A
X.XX ±0.20			比例 SCALE		产品料号 PART NO.	XD-XHD-2xNAW-X-XX	单位 UNITS	mm
X.XXX ±0.10			投影 Projection		材料 MATERIAL		页次 SHEET	1/1
1	初版发行	日期						
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE						