



TE Internal #: TAB62435501-001
M12 Pigtail Cable Assembly, 2 Position, .5 m, Industrial Fieldbus, PROFIBUS, Code B, M12 Socket, Shielded, Single Ended, PA66+25GF
[View on TE.com >](#)

Cable Assemblies > Copper Cable Assemblies > M8/M12 Cable Assemblies > Fieldbus,PROFIBUS M12B 2p PUR Drag Chain



M8/M12 Application Type: Industrial Fieldbus
Industrial Protocols: PROFIBUS
Number of Positions: 2
Connector & Keying Code: B
Connector Type (End A): M12 Socket
[All Fieldbus,PROFIBUS M12B 2p PUR Drag Chain \(32\)](#)

Features

Product Type Features

Connector Type (End A)	M12 Socket
Cable Assembly Type	M12 Pigtail

Configuration Features

Number of Positions	2
---------------------	---

Electrical Characteristics

Operating Voltage	250 VAC
-------------------	---------

Body Features

Cable Color	Violet
Connector Color (End A)	Black
Jacket Material	PUR
Conductor Material	Copper Alloy
Connector & Keying Code	B

Contact Features



Contact Current Rating (Max)	4 A
------------------------------	-----

Mechanical Attachment

Connector Orientation (End A)	Right Angle
-------------------------------	-------------

Housing Features

Housing Material	PA66+25GF
------------------	-----------

Dimensions

Outside Cable Diameter	7.8 mm
Wire Size	24 AWG

Operation/Application

M8/M12 Application Type	Industrial Fieldbus
Shielded	Yes

Industry Standards

IP Rating	IP67
Industrial Protocols	PROFIBUS

Packaging Features

Packaging Quantity	5
Packaging Method	Bag

Other

Cable Assembly Length	.5 m
Cable Assembly Configuration	Single Ended

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (1.9% in Component) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.



Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # TAB62635501-001
M12B2-MS-FR-PUR-0.5M



TE Part # 2273227-1
M12 x 1.0 angled plug 5pos shld B

Customers Also Bought



TE Part #1630184-9
YP10 47K 5%



TE Part #1879071-1
THS50 R01 5%



TE Part #T4171010402-001
M12,REAR MOUNTING,MALE,B,2P,0.2 M WIRE



TE Part #5-1393144-7
K10P-11D15-24=K10/K20

Documents

Product Drawings
M12B2-FR-PUR-0.5M

English

CAD Files
3D PDF
3D



Customer View Model

[ENG_CVM_CVM_TAB62435501-001_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_TAB62435501-001_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_TAB62435501-001_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[M8 / M12 Connector System Catalog](#)

English

[M8 / M12 Connector System Catalog](#)

Japanese

[M8/M12 Cable Assemblies Brochure](#)

English

Product Specifications

English

Product Environmental Compliance

[Product Compliance](#)

English

[Product Compliance](#)

English