

Specification Sheet

Part Number: 151-00982



Integrated design allows for easy insertion by hand.

1–3mm panel thickness range allows for multiple applications.

Double-compression design can accommodate up to 2 wires or cables of varying sizes.

Presents a high extraction force for withstanding extreme conditions.

Heavy Duty Metal Edge Clip, 1–3mm Panel Thickness, 5–7.6mm Cable Range, SS304, 100/bg

Article Number	151-00982
----------------	-----------

Type	MSC2
------	------

Color	Metal (ML)
-------	------------

Quantity Per	bag
--------------	-----

Product Description	HellermannTyton's Heavy Duty Metal Edge Clip provides an excellent alternative to managing up to 2 wire and PV cables where plastic fasteners are not the preferred method. Designed for effortless insertion, the Heavy Duty Edge Clip has a high extraction force that tolerates extreme environments and provides assurance that the cables are secure on a panel. This Metal Edge Clip is simple to install and can easily be removed with a flathead screwdriver.
---------------------	--

Short Description	Heavy Duty Metal Edge Clip, 1–3mm Panel Thickness, 5–7.6mm Cable Range, SS304, 100/bg
-------------------	---

Global Part Name	MSC2-SS304-ML
------------------	---------------

Length L (Imperial)	0.95
---------------------	------

Length L (Metric)	24.1
-------------------	------

Width W (Imperial)	0.50
--------------------	------

Width W (Metric)	13.0
------------------	------

Bundle Diameter Min (Imperial)	0.20
--------------------------------	------

Bundle Diameter Min (Metric)	5.0
------------------------------	-----

Bundle Diameter Max (Imperial)	0.30
--------------------------------	------

Bundle Diameter Max (Metric)	7.6
------------------------------	-----

Depth D (Imperial)	0.861
--------------------	-------

Depth D (Metric)	21.90
------------------	-------

Panel Thickness Min (Imperial)	0.04
--------------------------------	------

Panel Thickness Max (Imperial)	0.12
--------------------------------	------

Panel Thickness Min (Metric)	1.0
------------------------------	-----

Panel Thickness Max (Metric)	3.0
------------------------------	-----

Material	Stainless Steel (SS304)
Material Shortcut	SS304
Halogen Free	No
UV Resistant (Yes/No)	No
Operating Temperature	-112°F to +1000°F (-80°C to +538°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
UL Recognized (US)	Yes
UL Listed (US and Canada)	Yes
UL Recognized (US and Canada)	Yes
UL Listed (US)	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	7326908695

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)