

Specification Sheet

Part Number: TAG15-400

Tabtag dot matrix labels are specifically made for use in dot matrix printers for fast and easy printing.

Labels come with a pin-feed margin to ensure they can easily be loaded into any dot matrix printing system.

White dot matrix polyester has a matte finish, allowing for the highest resolution and print contrast using impact printers.

The acrylic-based adhesive bonds to a wide variety of substrates and can withstand high temperatures long term.



Dot Matrix Label, 1.0" x .50", 7 Across, Polyester, White, 5000/pkg

Article Number	595-15400
----------------	-----------

Type	TAG15
------	-------

Color	White (WH)
-------	------------

Quantity Per	pack
--------------	------

Product Description	HellermannTyton white polyester labels are ideal for marking small electrical and electronic components, such as EPROMS', Integrated circuits, as well as the circuit board itself. Printed labels can withstand the soldering process and survive flux removal when the board is washed. HellermannTyton's 400 material is designed for use on flat surfaces and can also be used to identify connectors, buttons and just about anything requiring permanent, durable, high temperature and UV resistant marking.
---------------------	---

Short Description	Dot Matrix Label, 1.0" x .50", 7 Across, Polyester, White, 5000/pkg
-------------------	---

Global Part Name	TAG15-400-WH
------------------	--------------

Width W (Imperial)	1.0
--------------------	-----

Width W (Metric)	25.4
------------------	------

Thickness T (Metric)	25.0
----------------------	------

Height H (Imperial)	0.50
---------------------	------

Height H (Metric)	12.70
-------------------	-------

Width of Liner (Metric)	218.40
-------------------------	--------

Width of Liner (Imperial)	8.6
---------------------------	-----

Material	Type 400, Polyester, white (400)
----------	----------------------------------

Material Shortcut	400
-------------------	-----

Adhesive	Acrylic
----------	---------

Halogen Free	No
--------------	----

UV Resistant (Yes/No)	No
-----------------------	----

Adhesive Operating Temperature	-40°F to +302°F (-40°C to +150°C)
--------------------------------	-----------------------------------

Operating Temperature	-40°F to +302°F (-40°C to +150°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL-Recognized
UL Recognized (US)	Yes
Package Quantity (Imperial)	5000
Package Quantity (Metric)	5000
Customs Number	3919905060
Labels per Column	7
Labels per Row	7

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)