




PCB LAYOUT



Specifications:

规格:

1.Voltage rating:250VAC/DC

额定电压: 250V AC/DC

2.Current rating:3A AC/DC

额定电流: 3A AC/DC

3.Withstanding voltage:500V AC/minute

耐受电压: ≥500V AC/分钟

4.Temperature range: -25℃~+80℃

温度范围: -25℃~+80℃

5.Insulation resistance:5000MΩMIN

绝缘电阻: ≥5000MΩ

6.Contact resistance:30mΩMax

接触电阻: ≥30mΩ

Material:

材料:

7.Rubber core:PBT UL94V-0

胶芯: PBT UL94V-0

8.The iron shell:SPCC Terminal half-Gold 15u Matte Tin

铁壳: SPCC 半金15u雾锡

B、成品不能有弯针，R角不一致等不良。

X02 09 W T 17 B X

① ② ③ ④ ⑤ ⑥ ⑦

- ① Series N0.
② Row No.Pin No.XX-09;
③ Welding Board Angle :W-Male
④ T: Tradutional
⑤ Planting Category: 17-Terminal half-Gold 15u Matte Tin
⑥ Color:B-BLACK
⑦ 5:TYPE-5; 7:TYPE-7

铆合方式	TYPE-7: 后铆鱼叉	TYPE-5: 铆鱼叉锁螺丝
图示		

						DSND		SCALE: N/A	MODEL TYPE: D-USB
ΔX					ANGLAR	±5°	DWN	VIEW:	PART NO.: X0209WT17BX
ΔX					L≤ 4	±0.2	CHKD	UNIT: mm/in	DWG NO.: X-X0209WT17BX
ΔX					4<L≤ 16	±0.3	APPD	SIZE: A4	
MARK	DESCRIPTION	DATE	REVISED	APPROVED	16<L≤ 63	±0.4			
					L> 63	±0.5			
REVISIONS					UNSPECIFIED TOLERANCES				
						XKB INDUSTRIAL PRECISION CO.,LIMITED			WEIGHT
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn									SHEET
									1/1
									REVISION
									A0