

product type designation

product description

antenna connection cable N-Connect/RSMA plug/plug

Connecting cable for SIMATIC NET antennas, preassembled

N-Connect/R-SMA male/ male flexible connection Pre-assembled cable, Length 0.3 m flexible connecting cable Access point antenna (RCoax and others).



suitability for use

Flexible connecting cable for connecting an antenna to an access point/client

wire length

0.3 m

electrical data

number of electrical connections

2

type of electrical connection

N-Connect/R-SMA male/male

transmission frequency

0 ... 6000 MHz

attenuation factor per length

- at 2.4 GHz / typical
- at 5.2 GHz / typical
- at 5.85 GHz / typical

0.53 dB/m
0.83 dB/m
0.89 dB/m

return loss

- minimum

23 dB

impedance

- rated value

50 Ω

capacity per length / at 1 kHz

82 pF/m

relative speed

82 %

mechanical data

design of the shield

Braided shield made of tin-plated copper wires

outer diameter

- of inner conductor
- of dielectric
- of cable sheath

1.4 mm
3.8 mm
6.3 mm

symmetrical tolerance of the outer diameter / of cable sheath

0.2 mm

thickness / of cable sheath

0.76 mm

material

- of inner conductor
- of dielectric
- of cable sheath

Cu
polyethylene foam
FRNC

color

- of cable sheath

pastel turquoise

bending radius

- with single bend / minimum permissible
- with multiple bends / minimum permissible

32 mm
45 mm

tensile load / maximum

80 N

weight per length

75 kg/km

ambient conditions

ambient temperature	
<ul style="list-style-type: none"> during operation during storage during transport during installation 	<p>-40 ... +80 °C</p> <p>-40 ... +80 °C</p> <p>-40 ... +80 °C</p> <p>-25 ... +80 °C</p>
chemical resistance	
<ul style="list-style-type: none"> to mineral oil 	conditional resistance
radiological resistance / to UV radiation	resistant
protection class IP	IP68; when plugged in
product features, product functions, product components / general	
product feature	
<ul style="list-style-type: none"> halogen-free silicon-free 	<p>Yes</p> <p>Yes</p>
standards, specifications, approvals	
certificate of suitability	
<ul style="list-style-type: none"> EAC approval RoHS conformity fire protection in accordance with EN 45545-2 	<p>Yes</p> <p>Yes</p> <p>No</p>
standard	
<ul style="list-style-type: none"> for fire behavior / flame resistance 	UL 1685 (Vertical tray), UL 1581 Sec. 1090 (H)
reference code	
<ul style="list-style-type: none"> according to IEC 81346-2 according to IEC 81346-2:2019 	<p>WG</p> <p>WGB</p>
further information / internet-Links	
Internet-Link	
<ul style="list-style-type: none"> to web page: selection aid TIA Selection Tool to website: Industrial communication to website: Industry Mall to website: Information and Download Center to website: Selection guide for cables and connectors to website: Image database to website: CAx-Download-Manager to website: Industry Online Support 	<p>http://www.siemens.com/tia-selection-tool</p> <p>http://www.siemens.com/simatic-net</p> <p>https://mall.industry.siemens.com</p> <p>http://www.siemens.com/industry/infocenter</p> <p>https://sie.ag/2QdlxcP</p> <p>http://automation.siemens.com/bilddb</p> <p>http://www.siemens.com/cax</p> <p>https://support.industry.siemens.com</p>

last modified:

7/7/2022 