



Product: [5301FH](#)

Security & Sound, 3 Conductor 18 AWG, TC, CMR

Product Description

Security & Commercial Audio Cable, 3 Conductor 18 AWG stranded (7x26) tinned copper conductors with polyolefin insulation, Beldfoil® shield and PVC jacket with ripcord, Riser rated.

Technical Specifications

Product Overview

Suitable Applications:	Intercom/PA Systems, Sound/Audio Systems
------------------------	--

Physical Characteristics (Overall)

Conductor				
AWG	Stranding	Material	Nominal Diameter	No. of Conductors
18	7x26	TC - Tinned Copper	.048 in	3
Conductor Count:				3

Insulation	
Material	Nominal Diameter
PP - Polypropylene	.062 in

Color Chart	
Number	Color
1	Black
2	Red
3	White

Outer Shield						
Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire Diameter	Drainwire AWG
Tape	Bi-Laminate (Alum+Poly)	Beldfoil®	100%	TC - Tinned Copper	0.020 in	24

Outer Jacket	
Material	Nominal Diameter
PVC - Polyvinyl Chloride	0.171 in

Electrical Characteristics

Conductor DCR	
Nominal Conductor DCR	Nominal Outer Shield DCR
6.5 Ohm/1000ft	16.9 Ohm/1000ft

Capacitance	
Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield
36 pF/ft	64.75 pF/ft

Current	
Max. Recommended Current [A]	

5 Amps per Conductor at 25°C

Voltage

UL Voltage Rating

300 V RMS

Temperature Range

UL Temp Rating:	75°C
Operating Temperature Range:	-5°C To +75°C

Mechanical Characteristics

Bulk Cable Weight:	26 lbs/1000ft
Max. Pull Tension:	58 lbs
Min. Bend Radius/Minor Axis:	1.7 in

Standards

NEC/(UL) Compliance:	CMR
CEC/C(UL) Compliance:	CMG

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive Compliance:	Yes

Suitability

Suitability - Burial:	No
Suitability - Hazardous Locations:	No
Suitability - Indoor:	Yes

Flammability, LS0H, Toxicity Testing

UL Flammability:	UL1666 Vertical Riser
------------------	-----------------------

Plenum/Non-Plenum

Plenum (Y/N):	No
Plenum Number:	6301FH

Related Part Numbers

Variants

Item #	Color	Put-Up Type	Length	UPC
5301FH 008500	Gray	Reel	500 ft	612825159445
5301FH 0081000	Gray	Reel	1,000 ft	612825159469
5301FH 008U1000	Gray	UnReel	1,000 ft	612825159483

Product Notes

Notes:	Ripcord under jacket
--------	----------------------

History

Update and Revision:	Revision Number: 0.56 Revision Date: 12-20-2022
----------------------	---

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.