





Specifications:
规格:
Current rating:5A AC/DC
额定电流: 5A AC/DC
Voltage rating:250V AC
额定电压: 250V AC
Withstanding voltage:500V AC/MIN
耐受电压: ≥500V AC/分钟
Temperature range:-55℃-+105℃
温度范围: -55℃-+105℃
Insulation resistance:1000MΩMIN
绝缘电阻: ≥1000MΩ
Contact resistance:30mΩMAN
接触电阻:≤30mΩ
Material And FINISHED:
材料和成本:
INSULATOR:PBT UL 94V-0
绝缘体: PBT UL 94V-0
SHELL: STEEL
外壳: 钢
CONTACT MATERIAL:BRASS
触点材料: 黄铜

X03 XX W T X X X H
① ② ③ ④ ⑤ ⑥ ⑦ ⑧

- ① Series N0.
② Row No.Pin No:XX-09
③ Welding Board Angle :W-Male
④ T: Traduitional
⑤ Planting Category: 1:Gold 1u ;2:Gold 2u; 3:Gold 3u ;4:Gold 5u; 5:Gold 15u;
6:Gold 30u ;7:Terminal half- Gold Bright Tin;8:Terminal half- Gold 2u Bright Tin
9:Terminal half- Gold 3u Bright Tin;10:Terminal half- Gold 5u Bright Tin
11:Terminal half- Gold 15u Bright Tin;12:Terminal half- Gold 30u Bright Tin
13:Terminal half- Gold Matte Tin;14:Terminal half- Gold 2u Matte Tin
15:Terminal half- Gold 3u Matte Tin;16:Terminal half- Gold 5u Matte Tin
17:Terminal half- Gold 15u Matte Tin;18:Terminal half- Gold 30u Matte Tin
⑥ B:Black W:White BL:Blue
⑦ 1:TYPE-1; 2:TYPE-2
⑧ H:Heightened



NO.OF CONTACT	A±0.20	B±0.20	C±0.20	D
09	16.92	24.99	30.81	11.08
15	25.25	33.32	39.14	19.39
25	38.96	47.04	53.04	33.24
37	55.42	63.50	69.32	49.86

DSND		SCALE: N/A	MODEL TYPE: D-USB		
DWN		VIEW: ④	PART NO.: X03XXWTXXXH		
CHKD		UNIT: mm/in	DWG NO.: X-X03XXWTXXXH		
APPD		SIZE: A4	WEIGHT	SHEET 1/1	REVISION A0

					ANGLAR	±5°
Δx					L≤ 4	±0.2
Δx					4<L≤ 16	±0.3
Δx					16<L≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L> 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						

XKB

XKB INDUSTRIAL PRECISION CO.,LIMITED