

ITEM NO.	PART NUMBER	DESCRIPTION	QTY.	COMPONENT NOTES
1	54-00098	Connector, 4 pin M5 plug, 5xL13mm, gold plated, panel mount, solder cup, IP67	1	nut and o-ring included
2	Wire	Wire, hook-up, TS, 26 AWG, UL 11028, 600V, 105C, 1 mm, mPPE	4	color: red, black, green, white
3	Heat shrink	Heat shrink, UL, black	4	covers solder joints






Notes:

Cable rated for 60 V, 1 A Temperature: -40 ~ 85 °C

IP67 waterproof rating when mated with corresponding (IP67) connector and installed properly in panel

Cables individually packaged in PE bag Functionally equivalent components may be substituted



Wiring Diagram				
54-00098	wire color (P/N)			
1	red (30-01772)			
2	black (30-01773)			
3	green (30-01777)			
4	white (30-01774)			

Revision:	Date:	Description:	Prepared:	Notes:	
A	11/10/2022	Initial release	Verified:	RoHS compliant  Function test: no open, no short circuit, no intermittent	
			Dimensions are in millimeters. Tolerances: X: ± 0.5 mm X.X: ± 0.3 mm X.XX: ± 0.05 mm	Description: Cable, 305 mm, M5 4C plug panel mount 54-00098 to blunt cut, 26 AWG, UL 11028 hook-up wire	
·		5	4	3	2

tel 1.541.323.3228 800 877.670.7118 fax 1.541.323.4202 web tensility.com

Size:	Part number:				
Α	10-05270				
Scale:	1.5:1		Sheet 1 of 1		

3 2