

# Data sheet

## 28657.6 KES-R 32/24 GR



Cable entry with membrane for unassembled cables, Mounting type: Rasten, Length: 147 mm, Width: 58 mm, IP66, Colour: Grey

**RAL:** Ähnlich 7035

### Business data

|                                            |                |
|--------------------------------------------|----------------|
| Article number                             | 28657.6        |
| Article name                               | KES-R 32/24 GR |
| GTIN (EAN)                                 | 4044211220341  |
| Packaging unit                             | 10             |
| Quantity unit                              | PC             |
| Weight per piece (not including packaging) | 73.8 g         |
| Weight per piece (including packaging)     | 73.8 g         |
| Unit of weight                             | G              |
| Customs number                             | 39259020       |
| Country of origin                          | DE             |
| Prio-Article                               | 28657.6        |
| Product description                        | Cable Entry    |

### Technical data

#### Dimensions

|                       |          |
|-----------------------|----------|
| Length                | 149.6 mm |
| Length of wall cutout | 112 mm   |
| Width                 | 58 mm    |
| Width of wall cutout  | 36 mm    |
| Installation height   | 14.5 mm  |

#### Materials

|                           |               |
|---------------------------|---------------|
| Material                  | Polyamide 6.6 |
| Glass-fibre reinforced    | ✓             |
| Flammability class UL 94  | V-0           |
| Working temperature, min. | -40 °C        |
| Working temperature, max. | 90 °C         |
| Sealing material          | TPE           |
| Halogen-free              | ✓             |
| Silicone-free             | ✓             |

#### Further technical data

|                                                   |         |
|---------------------------------------------------|---------|
| Mounting type                                     | Snap-on |
| Degree of protection for snap-in mounting         | IP54    |
| Sheet thickness min.                              | 1.5 mm  |
| Sheet thickness max.                              | 2 mm    |
| NEMA Type                                         | 1       |
| Number of wires                                   | 32      |
| Number of cables for cable diameters 3.2 - 6.3 mm | 32      |

Approvals

cUL Recognized

|                 |                 |
|-----------------|-----------------|
| cUL approval    | C22.2 No. 14-18 |
| cUL File Number | E489821         |
| cUL Recognized  | 1               |


UL Recognized

|                |         |
|----------------|---------|
| UL approval    | UL 508A |
| UL File Number | E489821 |
| UL Recognized  | 1       |
| UL Type Rating | 1       |

# Data sheet

## 28657.6 KES-R 32/24 GR

### Media



### Accessories

#### EMC brackets



Shield-connection rail enabling mounting of shield connection clips directly on cable entry system KDS and KES, Mounting type: Screw, Length: 35,3 mm, Width: 140 mm, Height: 16 mm, Profile: 10x3 mm

| Article number | Article name      | GTIN (EAN)    | Packaging unit |
|----------------|-------------------|---------------|----------------|
| <u>28626.0</u> | KDS-EMV-SAB 10/24 | 4044211219659 | 1 ST           |

#### Sheet-metal puncher



Sheet metal puncher for rectangular openings, Dimensions opening: 112 x 36 mm, Maximum wall thickness: 2.0 mm for stainless steel sheet, Material: steel

| Article number | Article name | GTIN (EAN)    | Packaging unit |
|----------------|--------------|---------------|----------------|
| <u>28752.0</u> | BL-VA KES    | 4044211221935 | 1 ST           |



Sheet metal puncher for rectangular openings, Dimensions opening: 112 x 36 mm, Maximum wall thickness: 2.0 mm for S 235 sheet, Material: steel

| Article number | Article name | GTIN (EAN)    | Packaging unit |
|----------------|--------------|---------------|----------------|
| <u>28744.0</u> | BL KES       | 4044211221942 | 1 ST           |