

## UK Computer Power Cord, C19 to BS1363, 13A, 250V, 16 AWG, 8 ft. (2.43 m), Black

MODEL NUMBER: P052-008



UK power cord delivers electricity from a BS 1363 wall outlet to a network device with a C20 inlet, such as a blade server, PDU or UPS.

### Features

**UK IEC Power Cord with C19 to BS 1363 Connection for Powering Network Devices** This BS 1363 power cord is designed for blade server chassis, switches, routers, PDUs, UPS systems and other network devices. It features a BS 1363 plug for connecting to a wall outlet and a C19 plug for connecting to a device. The 8-ft. (2.43 m) length allows you great flexibility in placing equipment with respect to the power outlet.

### Highlights

- Recommended for powering switches and other network devices
- BS 1363 plug connects to AC power; C19 plug connects to device's C20 inlet
- UK power cable is ideal replacement for worn-out or missing cord
- 8-ft. (2.43 m) length allows you greater freedom in placing devices away from outlet

### Applications

- Connect network devices like blade server chassis, switches, PDUs and UPS systems to a power outlet up to 2.4 m away in your data center
- Extend an existing power connection up to 2.4 m to more easily place a device or reach a power source in a rack
- Provide a high-quality replacement for a worn-out or missing power cord

### Package Includes

- P052-008 UK Power Cable with BS 1363 Plug, 8-ft. (2.43 m), Black

## Specifications

OVERVIEW	
UPC Code	037332141996
Device Compatibility	Server; Router; Network Switch; UPS; PDU
Country/Region	UK
INPUT	
Maximum Input Amps	13
Voltage Compatibility (VAC)	250
PHYSICAL	
Plug Color	Black
Cable Jacket Color	Black

Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	8.4mm
Number of Conductors	3
Wire Gauge (AWG)	16
Wire Gauge (OD - mm <sup>2</sup> )	1.29
Cable Length (ft.)	8
Cable Length (m)	2.44
Shipping Dimensions (hwd / in.)	0.25 x 5.70 x 6.90
Shipping Dimensions (hwd / cm)	0.64 x 14.48 x 17.53
Shipping Weight (lbs.)	0.90
Shipping Weight (kg)	0.41
Unit Dimensions (hwd / in.)	0.250 x 5.700 x 6.900
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	14° to 140°F (-10° to 60°C)
Storage Temperature Range	14° to 140°F (-10° to 60°C)
Operating Humidity Range	35% to 85% RH, Non-Condensing
Storage Humidity Range	35% to 85% RH, Non-Condensing
<b>CONNECTIONS</b>	
Side A - Connector 1	BS1363 UK PLUG
Side B - Connector 1	IEC-320-C19
<b>FEATURES &amp; SPECIFICATIONS</b>	
Antibacterial	No
Angled Plug	No
High Voltage	Yes
Locking Plug	No
Coiled Power Cord	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	cUL Listed; UL Listed
Product Compliance	CE (Europe); REACH; RoHS; UKCA
<b>WARRANTY &amp; SUPPORT</b>	



1000 Eaton Boulevard  
Cleveland, OH 44122  
United States

Product Warranty Period (Worldwide)	Lifetime limited warranty
--	---------------------------



© 2023 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.