


Specifications:
 规格:
 Current rating:5A AC/DC
 额定电流: 5A AC/DC
 Voltage rating:250V AC
 额定电压: 250V AC
 Withstanding voltage:500V AC/MIN
 耐受电压: ≥500V AC/分钟
 Temperature range:-55℃~+105℃
 温度范围: -55℃~+105℃
 Insulation resistance:1000MΩMIN
 绝缘电阻: ≥1000MΩ
 Contact resistance:30mΩMAN
 接触电阻:≤30mΩ
 Material And FINISHED:
 材料和成本:
 INSULATOR:PBT UL 94V-0
 绝缘体: PBT UL 94V-0
 SHELL: STEEL
 外壳: 钢
 CONTACT MATERIAL:BRASS
 触点材料: 黄铜

X03 XX F T X X X H
 ① ② ③ ④ ⑤ ⑥ ⑦ ⑧

- ① Series NO.
- ② Row No.Pin No:XX-09,15,25,37
- ③ Welding Board Angle :F-Female
- ④ T: Traduitional
- ⑤ Planting Category: 1:Gold 1u ;2:Gold 2u; 3:Gold 3u ;4:Gold 5u; 5:Gold 15u; 6:Gold 30u ;7:Terminal half- Gold Bright Tin;8: Terminal half- Gold 2u Bright Tin 9: Terminal half- Gold 3u Bright Tin;10: Terminal half- Gold 5u Bright Tin 11: Terminal half- Gold 15u Bright Tin;12: Terminal half- Gold 30u Bright Tin 13: Terminal half- Gold Matte Tin;14:Terminal half- Gold 2u Matte Tin 15:Terminal half- Gold 3u Matte Tin ;16:Terminal half- Gold 5u Matte Tin 17:Terminal half- Gold 15u Matte Tin;18:Terminal half- Gold 30u Matte Tin
- ⑥ B:Black W:White BL:Blue
- ⑦ 1:TYPE-1; 2:TYPE-2
- ⑧ H:Heightened



NO.OF CONTACT	A±0.20	B±0.20	C±0.20	D
09	16.34	24.99	30.81	11.08
15	24.66	33.32	39.14	19.39
25	38.38	47.04	53.04	33.24
37	54.84	63.50	69.32	49.86

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
ΔX					ANGULAR ±5°
ΔX					L ≤ 4 ±0.2
ΔX					4 < L ≤ 16 ±0.3
					16 < L ≤ 63 ±0.4
					L > 63 ±0.5



DSND		SCALE: N/A	MODEL TYPE: D-USB
DWN		VIEW:	PART NO.: X03XXFTXXXH
CHKD		UNIT: mm/in	DWG NO.: X-X03XXFTXXXH
APPD		SIZE: A4	WEIGHT SHEET REVISION
			1/1 A0