

USB-C Flat Cable (M/M), USB 2.0, Black, 3 ft. (0.91 m)

MODEL NUMBER: U040-003-C-FL



Flat USB cable connects a smartphone or other USB-C device to the USB-C port on your computer, charger or power bank.

Features

Flat USB 2.0 Cable Charges and Syncs Your Phone or Other USB-C Mobile Device This USB sync/charge cable (M/M) connects your smartphone, tablet, MacBook Pro, Windows laptop or other USB-C device to the USB-C port on a computer, docking station or wall charger. It supports power output up to 3 amps (60 watts), which is sufficient for fast charging and powering most mobile devices. It also simultaneously synchronizes and transfers data at USB 2.0 speeds up to 480 Mbps.

Innovative Flat Cable Prevents Tangles, Allows Flexible Bends Very flexible for convenient on-the-go connections, this flat cable avoids nasty tangles in your backpack or laptop bag. Its advanced flat design allows easy rolling for tangle-free storage. Plus, it bends easily for connecting to devices in tight spaces or around obstacles.

Reversible USB-C Connectors Attach in Either Direction Unlike traditional USB cables that connect in only one direction, the reversible USB-C male connectors plug into a USB-C or Thunderbolt 3 port in either direction for an instant connection every time.

Specifications

OVERVIEW	
UPC Code	037332254009
Technology	USB 2.0 (High Speed)
Cable Type	Passive
INPUT	

Highlights

- Flexible flat design helps prevent inconvenient tangling and allows easy bending
- Supports USB 2.0 speeds up to 480 Mbps to ensure efficient charging and data transfers
- Supports 3A (60W) power output for charging, syncing and powering mobile devices
- Reversible USB-C plugs connect in either direction for immediate no-fuss use
- Flat USB-C cable is compatible with all USB-C and Thunderbolt 3 devices

Applications

- Charge and power your MacBook Pro, Windows laptop or other USB-C or Thunderbolt 3 device from a USB-C wall charger up to 3 ft. away
- Transfer data between an external hard drive and your laptop or PC
- Connect your laptop to a docking station or hub with a USB-C or Thunderbolt 3 port
- Roll tightly for convenient carrying in your laptop bag, backpack or briefcase as a flexible spare cable

System Requirements

- Devices with USB-C or Thunderbolt 3 ports

Package Includes

- U040-003-C-FL USB-C to USB-C Cable, M/M, Black, 3 ft. (0.9 m)

Maximum Input Amps	3
Maximum Input Watts	60
POWER	
USB Power Delivery (PD) Charging Support	Yes
PHYSICAL	
Material of Construction	PVC
Cable Jacket Color	Black
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	2.1*5.8 MM
Wire Gauge (AWG)	30/24
Cable Length (ft.)	3
Cable Length (m)	0.91
Cable Length (in.)	36
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.60
Shipping Weight (kg)	0.27
Unit Packaging Type	Polybag
ENVIRONMENTAL	
Operating Temperature Range	32° to 113°F (0° to 45°C)
Storage Temperature Range	-40° to 158°F (-40° to 70°C)
Operating Humidity Range	10% to 85%, Non-Condensing
Storage Humidity Range	5% to 90%, Non-Condensing
CONNECTIONS	
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	USB C (MALE)
Connector Plating	Nickel
Contact Plating	Gold
Connector Style	Straight
FEATURES & SPECIFICATIONS	
USB Specification	USB 2.0 (up to 480 Mbps)

STANDARDS & COMPLIANCE	
Product Compliance	RoHS; REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty