



PCB LAYOUT

SPECIFICATIONS

- 1. **Current Rating:** 7A AC, DC
- 2. **Voltage Rating:** 250V AC, DC
- 3. **Temperatuer Range:** -25℃~+85℃
- 4. **Contact Resistance:** 20mΩ Max
- 5. **Insulation Resistance:** 1000MΩ Min
- 6. **Withstanding Voltang:** 1500V AC/minute
- 7. **Material:** Wafer Nylon66, UL94V-0
PIN Brass Tin-plated

Circuit	Part NO.	Dimensions mm	
		A	B
2	HC-VH-2A2	3.96	7.92
3	HC-VH-3A2/ HC-VH-3A3	7.92	11.88
4	HC-VH-4A4	11.88	15.84
5	HC-VH-5A5	15.84	19.80
6	HC-VH-6A6	19.80	23.76
7	HC-VH-7A7	23.76	27.72
8	HC-VH-8A8	27.72	31.68
9	HC-VH-9A9	31.68	35.64
10	HC-VH-10A10	35.64	39.60

		GENERAL TOLERANCE		制图 DRAWING		深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO., LTD			
		DIM TOL		审核 CHECK					
		X.X ±0.30		批准 APPROVAL		产品名称 TITLE	VH 直针	版本 REV.	A
1 初版发行		X.XX ±0.20		比例 SCALE		产品料号 PART NO.	HC-VH-NAN	单位 UNITS	mm
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle ±3.0°	投影 Projection		材料 MATERIAL		页次 SHEET	1/1