

High-Speed HDMI Cable with 2 Right-Angle Connectors, Digital Video with Audio (M/M), 6 ft. (1.83 m)

MODEL NUMBER: P568-006-RA2



Highlights

- Features right-angle connectors on both ends; ideal for tight locations
- Supports iPad2 Video Mirroring when used with Apple Digital AV Adapter
- Gold-plated connectors provide optimal signal transfer
- Bandwidth up to 18 Gbps Full 1080p resolution
- High Speed HDMI and HDCP compliant

Package Includes

 6-ft. High Speed HDMI Gold Cable with Right-Angle Connectors

Features

- · Features right-angle connectors on both ends; ideal for tight locations
- Supports iPad2 Video Mirroring when used with Apple Digital AV Adapter
- Gold-plated connectors provide optimal signal transfer
- Premium double-shielded cable protects against outside noise (EMI/RFI)
- Impedance-matched twisted-pair construction reduces cross-talk and interference
- Bandwidth up to 18 Gbps Full 1080p resolution
- Perfect for connecting an iPad2 to an HDTV (video mirroring) to watch movies, play games, surf the web and display presentations

Specifications

OVERVIEW		
UPC Code	037332146090	
Product Type	Passive Cable	
Technology	HDMI	
Cable Type	Passive	
VIDEO		
Max Supported Video Resolution	1920 x 1200 (1080p)	
Max Supported Color Depth	48-bit Deep Color	
HDR Support	No	



3D Video Supported	No	
Chroma Sub Sampling	4:4:4	
EDID Support	Yes	
Signal Transmission	Bidirectional	
AUDIO		
Audio Specification	DTS-HD	
USER INTERFACE, ALERTS & CONTROLS		
LED Indicators	0	
PHYSICAL		
Color	Black	
Material of Construction	PVC	
Cable Jacket Color	Black	
Connector Color	Black	
Cable Jacket Material	PVC	
Cable Jacket Rating	VW-1	
Cable Outer Diameter (OD)	5.5 mm	
Wire Gauge (AWG)	30	
Cable Length (ft.)	6	
Cable Length (m)	1.83	
Cable Length (in.)	72	
Ferrite Core	No	
Minimum Bend Radius	27.5mm	
Shipping Dimensions (hwd / in.)	7.00 x 9.00 x 0.50	
Shipping Dimensions (hwd / cm)	17.78 x 22.86 x 1.27	
Shipping Weight (lbs.)	0.30	
Shipping Weight (kg)	0.14	
ENVIRONMENTAL		
Operating Temperature Range	14° to 122°F (-10° to 50°C)	
Storage Temperature Range	5° to 140°F (-15° to 60°C)	
Operating Humidity Range	0% to 90% RH, Non-Condensing	
Storage Humidity Range	0% to 90% RH, Non-Condensing	
COMMUNICATIONS		



EDID Compatible	Yes	
Consumer Electronics Control (CEC) Supported	Yes	
CONNECTIONS		
Side A - Connector 1	HDMI (MALE)	
Side B - Connector 1	HDMI (MALE)	
Connector Plating	Gold	
Contact Plating	Gold	
Connector Style	Angled	
Latching or Gripping Connector	No	
FEATURES & SPECIFICATIONS		
EMI/RFI Line Noise Protection	No	
MST Support	No	
Antibacterial	No	
IP68 Rated	No	
IP20 Rated	No	
Armored Cable	No	
Ethernet Support	No	
HDCP Specification	1.4; 2.2	
STANDARDS & COMPLIANCE		
Product Compliance	RoHS; REACH	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	



© 2023 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.