

Specification Sheet

Part Number: 157-00325



Offset design positions bundles away from obstructions, heat or sources of abrasion.

Four-pawl, three-tooth design delivers outstanding stud retention to keep bundles secure.

Offset M5/M6 Stud Mount Tie, 7.5" Tie, 50lb Tensile Strength, PA66HIRHS, BK, 2000/pkg

Article Number

157-00325

Type

T50ROSM6SMSO25

Color

Black (BK)

Quantity Per

carton

Product Description

One-piece cable ties with stud mount feature an offset design that positions bundles away from obstructions, heat or sources of abrasion. With their low insertion force and high extraction performance, HellermannTyton mounting ties offer the ideal combination of high-grade materials and superior design to suit the mounting and bundling needs of complex applications. Available in standard and high-heat material options.

Short Description

Offset M5/M6 Stud Mount Tie, 7.5" Tie, 50lb Tensile Strength, PA66HIRHS, BK, 2000/pkg

Global Part Name	T50ROSM6SMSO25-PA66HIRHSUV-BK
------------------	-------------------------------

Minimum Tensile Strength (Imperial)	50.0
-------------------------------------	------

Minimum Tensile Strength (Metric)	222.0
-----------------------------------	-------

Length L (Imperial)	8.8
---------------------	-----

Length L (Metric)	223.52
-------------------	--------

Offset Length (Imperial)	1.0
--------------------------	-----

Offset Length (Metric)	25.5
------------------------	------

Fixation Method	Stud Mount
-----------------	------------

Identification Plate Position	none
-------------------------------	------

Releasable Closure	No
--------------------	----

Tie Closure	plastic pawl
-------------	--------------

Width W (Imperial)	0.56
--------------------	------

Width W (Metric)	14.2
------------------	------

Bundle Diameter Min (Imperial)	0.08
--------------------------------	------

Bundle Diameter Min (Metric)	2.0
------------------------------	-----

Bundle Diameter Max (Imperial)	1.97
--------------------------------	------

Bundle Diameter Max (Metric)	50.0
Cable Ties	157-00325
Height H (Imperial)	0.59
Height H (Metric)	15.0
Mounting Hole Diameter D (Imperial)	0.24" x 0.04
Mounting Hole Diameter D (Metric)	M6 x 1
Stud Diameter (Metric)	6.0 mm 5.0 mm
Stud Diamater (Imperial)	0.20 ", 0.24
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes

ROHS Compliant	Yes
Package Quantity (Imperial)	2000
Package Quantity (Metric)	2000
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)