



Product: [35718](#)

Lead Wire, #18 Str TC, XLPO Ins, AWM 3199

Request Sample

Product Description

Low Temp Rubber Lead Wire, 18AWG (19x30H) Tinned Copper, XLPO Insulation, AWM 3199 CSA TYPE CL1054 300V 105C

Technical Specifications

Product Overview

Suitable Applications:	internal wiring of appliances and ballast leads
------------------------	---

Physical Characteristics (Overall)

Conductor			
AWG	Stranding	Material	No. of Conductors
18	19x30.5	TC - Tinned Copper	1
Conductor Count:		1	

Insulation		
Material	Nominal Diameter	Nominal Wall Thickness
XLP, XLPO, XLPE (Thermoset)	0.078 in	0.016 in

Electrical Characteristics

Voltage
UL Voltage Rating
300 V RMS

Temperature Range

UL Temp Rating:	105°C
-----------------	-------

Mechanical Characteristics

Recommended Max Baking Cycles:	24 Hours @ 300°F (149°C) ~ 12 Hours @ 325°F (163°C) ~ 8 Hours @ 350°F (177°C)
Bulk Cable Weight:	8 lbs/1000ft
Min. Bend Radius/Minor Axis:	0.32 in

Standards

UL AWM Style Compliance:	AWM 3199
CSA Rating:	300 V RMS, 105°C
CSA Type:	CL1054

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes

EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
CA Prop 65:	Yes
MII Order #39 (China RoHS):	Yes

Flammability, LSOH, Toxicity Testing

UL voltage rating:	300 V RMS
--------------------	-----------

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Related Part Numbers

Variants

Item #	Color	Put-Up Type	Length	UPC
35718 0105000	Black	Reel	5,000 ft	612825145370
35718 0015000	Brown	Reel	5,000 ft	612825145349
35718 0055000	Green, Dark	Reel	5,000 ft	612825145356
35718 0095000	White	Reel	5,000 ft	612825145363

Footnote:	C - CRATE REEL PUT-UP., I - MAY CONTAIN MORE THAN 1 PIECE. MINIMUM LENGTH OF ANY ONE PIECE IS 200'. U - TOPCOAT ADDERS ON STOCK SOLID COLORS. MINIMUM ORDER 10,000' PER COLOR COMBINATION. (SEE TOPCOAT ADDER TABLE), Z - FINAL PUT-UP MAY VARY (= OR -) 10% FOR SPOOLS OR REELS AND (+ OR -) 5% FOR UNREEL CARTONS FROM LENGTH SHOWN.
-----------	--

History

Update and Revision:	Revision Number: 0.359 Revision Date: 05-05-2023
----------------------	--

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.