

WP-G BRASS IP65 M32 - Screw connection



3241063

<https://www.phoenixcontact.com/us/products/3241063>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable gland made from brass with metric thread, IP65 protection

Commercial data

Item number	3241063
Packing unit	1 pc
Minimum order quantity	2 pc
Sales key	BF68
Product key	BF7DSA
Catalog page	Page 600 (C-3-2019)
GTIN	4046356712132
Weight per piece (including packing)	115.5 g
Weight per piece (excluding packing)	115.5 g
Customs tariff number	74122000
Country of origin	DE

WP-G BRASS IP65 M32 - Screw connection



3241063

<https://www.phoenixcontact.com/us/products/3241063>

Technical data

Product properties

Product type	Corrugated pipe screw connection
Type of the screw connection	Conduit adapter
Type	Outer thread
Cable outlet	straight
Thread type	metric

Dimensions

Width	48 mm
Height	43 mm
Length	43 mm
Wrench size for mounting	43 mm
	45 mm

External dimensions

Outside diameter	36 mm
------------------	-------

Internal dimensions

Internal diameter	27.5 mm
-------------------	---------

Material specifications

Material	Brass, nickel-plated
Material for screw connection	Brass, nickel-plated
Components	halogen-free

Mechanical properties

Mechanical data

Type of the screw connection	Conduit adapter
------------------------------	-----------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
Ambient temperature (operation)	-40 °C ... 125 °C

Mounting

Wrench size	43 mm
-------------	-------


WP-G BRASS IP65 M32 - Screw connection



3241063

<https://www.phoenixcontact.com/us/products/3241063>

Approvals

 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3241063>



VDE Zeichengenehmigung

WP-G BRASS IP65 M32 - Screw connection



3241063

<https://www.phoenixcontact.com/us/products/3241063>

Classifications

ECLASS

ECLASS-11.0	27430310
ECLASS-13.0	27430310
ECLASS-12.0	27430310

ETIM

ETIM 8.0	EC001180
----------	----------

UNSPSC

UNSPSC 21.0	40141700
-------------	----------

WP-G BRASS IP65 M32 - Screw connection



3241063

<https://www.phoenixcontact.com/us/products/3241063>

Environmental product compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50 years
	For information on hazardous substances, refer to the manufacturer's declaration available under "Downloads"

WP-G BRASS IP65 M32 - Screw connection

3241063

<https://www.phoenixcontact.com/us/products/3241063>



Accessories

WP-STEEL PVC C 36 - Protective hose

3240872

<https://www.phoenixcontact.com/us/products/3240872>



Protective hose, material: Steel, galvanized / PVC, degree of protection: IP68, color: black, inner diameter: 29 mm, Total length: 10 m

WP-BASE A M32 - Protective hose fixing bracket

3241086

<https://www.phoenixcontact.com/us/products/3241086>



Fixing bracket for protective sleeves, fixed with two screws

Phoenix Contact 2023 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com