


Product data sheet

Specifications

Cable duct - 50 x 50 mm - without cover - grey



AK2GD5050

Main

Product or component type	Cable duct
Accessory / separate part category	Cabling accessories
Range compatibility	Spacial (S3D) Spacial (CRN) Thalassa PLA Thalassa PLS Thalassa PLM
Device composition	Without cover
Quantity per set	Set of 8

Complementary

Colour	Grey RAL 7030)
Fixing mode	Clip-on support By screws
Material	PVC (polyvinyl chloride)
Height	1.97 in (50 mm)
Length	78.74 in (2000 mm)
Width	1.97 in (50 mm)
Net weight	1.32 lb(US) (0.6 kg)
Total number of wires	160

Environment

Ambient air temperature for operation	23...140 °F (-5...60 °C)
Flame retardance	V-0 UL 94
Fire resistance	1760 °F (960 °C) IEC 60695-2-1/1
Standards	VDE 0506 VDE 0660 DIN 43659

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.77 in (4.500 cm)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Width	1.77 in (4.500 cm)
Package 1 Length	78.74 in (200.000 cm)
Package 1 Weight	18.59 oz (527.000 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	8
Package 2 Height	3.74 in (9.500 cm)
Package 2 Width	3.94 in (10.000 cm)
Package 2 Length	78.74 in (200.000 cm)
Package 2 Weight	9.68 lb(US) (4.391 kg)
Unit Type of Package 3	P2M
Number of Units in Package 3	384
Package 3 Height	17.72 in (45.000 cm)
Package 3 Width	78.74 in (200.000 cm)
Package 3 Length	47.24 in (120.000 cm)
Package 3 Weight	479.21 lb(US) (217.368 kg)

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
RoHS exemption information	Yes

Contractual warranty

Warranty	18 months
----------	-----------

Recommended replacement(s)