


- 1、Current Rating: 1A AC, DC
- 2、Voltage Rating: 50V AC, DC
- 3、Temperatuer Range: -25℃~ +85℃
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 100mΩ Min
- 6、Withstanding Voltang: 500V AC/minute
- 7、Material: Wafer LCP UL94-VO

Qty/Reel: 1500 PCS

Circuit	Part NO.	Dimensions mm		
		A	B	C
2	XD-1.0-2PWT-XX	1.00	4.30	2.60
3	XD-1.0-3PWT-XX	2.00	5.30	3.60
4	XD-1.0-4PWT-XX	3.00	6.30	4.60
5	XD-1.0-5PWT-XX	4.00	7.30	5.60
6	XD-1.0-6PWT-XX	5.00	8.30	6.60
7	XD-1.0-7PWT-XX	6.00	9.30	7.60
8	XD-1.0-8PWT-XX	7.00	10.30	8.60
9	XD-1.0-9PWT-XX	8.00	11.30	9.60
10	XD-1.0-10PWT-XX	9.00	12.30	10.60
11	XD-1.0-11PWT-XX	10.00	13.30	11.60
12	XD-1.0-12PWT-XX	11.00	14.30	12.60
13	XD-1.0-13PWT-XX	12.00	15.30	13.60
14	XD-1.0-14PWT-XX	13.00	16.30	14.60
15	XD-1.0-15PWT-XX	14.00	17.30	15.60
16	XD-1.0-16PWT-XX	15.00	18.30	16.60



XD - 1.0 - N*** - **



			GENERAL TOLERANCE	制 图 DRAWING	03	 深圳讯答科技有限公司 ShenzhenXundaTechnology Co.,Ltd				
			DIM TOL	审 核 CHECK						
			X.X ±0.30	批 准 APPROVAL		产品名称 TITLE	1.0 单排 卧贴	版本 REV.	A	
1	初版发行		X.XX ±0.20	比 例 SCALE		产品料号 PART NO.	XD-1.0-NPWT-XX	单位 UNITS	mm	
			X.XXX ±0.10							
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle ±3.0°	投 影 Projection		材 料 MATERIAL		页 次 SHEET	1/	