







Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)



SPECIFICATIONS

Rated Current:3.0AMP

Contact Resistance:20mΩ Max

Withstand Voltage:1000V AC/DC

Insulation Resistance:1000MΩ Min

Operation Temperature:-40°c to +105°c

Contact Material:Brass

Contact Plating:Au or Sn Over Ni

Insulator Material:Polyester(UL94V-0)

Standard: PA6T

Max.Processing Temp: 230°C for 30-60 seconds
(260°C for 10 seconds)

Dimension antitheses list

ITEM	PA	PB	PC	L
Standard	6.00	6.90	3.00	12.90
Alternate				

Ordering Information

XDZ 254 - * - N - W - * - **					
No. of Rows 1=Single Row 2=Dual Row	No. of Pins 02-40 Pin	Type Z=直针 W=弯针 S=贴片 WS=弯插	Length mm	Contact Plating G0:Gold Plating G1:1u" Gold G2:3u" Gold G3:5u" Gold G4:10u" Gold G5:15u" Gold G6:30u" Gold S0:Gold Plating/Tin S1:1m	

			GENERAL TOLERANCE		制图 DRAWING	 深圳讯答科技有限公司 ShenzhenXundaTechnology Co.,Ltd			
			DIM	TOL	审核 CHECK				
			XX	±0.30	批准 APPROVAL	产品名称 TITLE	2.54 双排 正弯排针 塑高2.5	版本 REV.	A
			X.XX	±0.20	比例 SCALE	产品料号 PART NO.	XDZ254-2-N-W-2.5-XX	单位 UNITS	mm
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle ±3.0°		投影 Projection	材料 MATERIAL		页次 SHEET	1/1