
ITEM NO.	PART NUMBER	DESCRIPTION		COMPONENT NOTES
1	54-00296	Connector, 3 pin M8 A-code socket, 8x18.7 mm, gold plated, panel mount, solder cup, IP67	1	nut and o-ring included
2	Wire	Wire, hook-up, TS, 24 AWG, UL 11028, 600V, 105C, 1.1 mm, mPPE	3	color: red, black, white
3	Heat shrink	Heat shrink, UL, black	3	covers solder joints



Notes:

Cable rated for 60 V, 3 A Temperature: -40 ~ 105 °C

IP67 waterproof rating when mated with corresponding (IP67) connector and installed properly in panel

Cables individually packaged in PE bag Functionally equivalent components may be substituted



Front View Not to Scale

Wiring Diagram				
54-00296	wire color (P/N)			
1	red (30-01762)			
3	black (30-01763)			
4	white (30-01764)			

Revision:	Date:	Description:	Prepared:	Prepared: Notes:					
Α	10/20/2022	Initial release		RoHS compliant	TFNSILITY			ITY	
			Verified:	Function test: no open, no short circuit, no intermittent		tel 1.541.323.3228 800 877.670.7118 fax 1.541.323.4202 web tensility.com			
			Dimensions are in millimeters. Tolerances: X: ± 0.5 mm	Description: Cable, 305 mm, M8 3C socket panel mount 54- 00296 to blunt cut, 24 AWG, UL 11028 hook-up wire	Size: Part number: A 10-05203				
			X.X: ± 0.3 mm X.XX: ± 0.05 mm		Scale:	1.5:1		Sheet 1 of 1	

5 4 2