

Specification Sheet

Part Number: 115-00145



Provides dual separation between bundles to prevent chafing and abrasion.

150lb tensile strength ensures enough strength for heavy duty applications.

Straps are releasable for increased serviceability.

Dual Clamp Tie w/Neoprene Sleeving, 0.25" Stud Dia, 2.30" Max Bundle Dia,150lb, PA66HIRHSUV, Black, 500/pkg

Article Number	115-00145
----------------	-----------

Type	DCT11SLVH1
------	------------

Color	Black (BK)
-------	------------

Quantity Per	bag
--------------	-----

Product Description	Dual-Clamp Ties are designed to provide parallel separation between hoses, wires, cables, and tubing to protect them from abrasion. These ties have an optional mounting hole for securing bundles along the chassis of trucks, trailers, and heavy-duty equipment. The unique one-piece design features the dual head centered on the strap.
---------------------	---

Short Description	Dual Clamp Tie w/Neoprene Sleeving, 0.25" Stud Dia, 2.30" Max Bundle Dia,150lb, PA66HIRHSUV, Black, 500/pkg
-------------------	---

Global Part Name	DCT11SLVH1-PA66HIRHSUV-BK
------------------	---------------------------

Minimum Tensile Strength (Imperial)	150.0
Minimum Tensile Strength (Metric)	667.0
Length L (Imperial)	19.25
Length L (Metric)	489.0
Fixation Method	Weld Stud Fixing
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.504
Width W (Metric)	12.8
Bundle Diameter Min (Imperial)	0.20
Bundle Diameter Min (Metric)	6.4
Bundle Diameter Max (Imperial)	2.28
Bundle Diameter Max (Metric)	58.0
Height H (Imperial)	0.75

Height H (Metric)	19.1
Mounting Hole Diameter D (Imperial)	0.20
Mounting Hole Diameter D (Metric)	6.2 mm
Mounting Hole Diameter D Min (Imperial)	0.20
Mounting Hole Diameter D Max (Imperial)	0.20
Mounting Hole Diameter D Max (Metric)	6.2
Stud Diameter (Metric)	6.35 mm
Stud Diameter (Imperial)	0.25

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
UV Resistant (Yes/No)	Yes
Reach Compliant (Article 33)	No
ROHS Compliant	Yes

Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)