

Power Cord, NEMA 5-15P to Right-Angle C15 - Heavy-Duty, 15A, 125V, 14 AWG, 8 ft. (2.43 m), Black

MODEL NUMBER: P019-008-C15RA



C15 right-angle power cable connects a PoE network switch or other device with a C16 power inlet in tight spaces or awkward angles.

Features

IEC C15 Power Cord for Network Devices That Require a Heavy-Gauge Connection This IEC C15 power cable features 14 AWG wire suitable for high power connections, making it reliable for large server applications that require a higher-rated, heavier-gauge cable. The C15 connector is designed for higher-temperature devices, such as electric kettles, PoE (Power over Ethernet) switches with high-wattage power supplies, and similar network components. This cord can also replace or upgrade the standard power cord provided by the device's manufacturer. The 8-ft. (2.43 m) length allows you flexibility in placing equipment with respect to the power outlet.

Right-Angle C15 Plug Makes Connecting in Tight Spaces Easier The C15 right-angle power cable is easier to install in confined spaces, such as the back of a rack enclosure cabinet. When plugged in, the right-angled C15 plug guides the cable parallel to your peripheral, allowing you to push the device up against a wall or hide it behind a desk to maximize space.

Highlights

- Right-angle C15 plug allows easier connection in confined or hard-to-reach spaces
- Recommended for powering PoE switches with high-wattage power supplies
- 8-ft. (2.43 m) length allows flexibility in placing devices in relationship to AC outlet
- NEMA 5-15P to C15 cable replaces or upgrades original manufacturer's power cord
- Thick 14 AWG wire gauge manages high power levels required for larger equipment

Applications

- Connect devices like high-wattage PoE switches to a PDU up to 8-ft. (2.43 m) away in your data center
- Extend an existing power connection up to 8-ft. (2.43 m) to more easily place a device or reach a power source
- Update or replace the standard power cord provided by a device's original manufacturer
- Power a device located in a hard-to-access area behind a desk or flush against a wall

Package Includes

- P019-008-C15RA 5-15P to Right-Angle C15 Power Cord, 8-ft. (2.43 m), Black

Specifications

OVERVIEW	
UPC Code	037332202413
Device Compatibility	Computer; Server; Network Switch; UPS; PDU
Country/Region	North America
INPUT	
Maximum Input Amps	15
Voltage Compatibility (VAC)	125

PHYSICAL	
Plug Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	9.2mm
Number of Conductors	3
Wire Gauge (AWG)	14
Wire Gauge (OD - mm ²)	2.08
Cable Length (ft.)	8
Cable Length (m)	2.44
Shipping Dimensions (hwd / in.)	0.50 x 11.80 x 14.00
Shipping Dimensions (hwd / cm)	1.27 x 29.97 x 35.56
Shipping Weight (lbs.)	1.00
Shipping Weight (kg)	0.45
ENVIRONMENTAL	
Operating Temperature Range	-4° to 140°F (-20° to 60°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Operating Humidity Range	10% to 65% RH
Storage Humidity Range	10% to 65% RH
CONNECTIONS	
Side A - Connector 1	NEMA 5-15P
Side B - Connector 1	IEC-320-C15 – RIGHT ANGLE
FEATURES & SPECIFICATIONS	
Antibacterial	No
Angled Plug	Yes
High Voltage	No
Locking Plug	No
Coiled Power Cord	No
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL Listed

Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty