

SAC-4P-M 8MS/ 1,0-PUR/M 8FSSH - Sensor/actuator cable



1574593

<https://www.phoenixcontact.com/us/products/1574593>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 4-position halogen-free, shielded, Plug straight M8, coding: A, on Socket straight M8, cable length: 1 m

Commercial data

Item number	1574593
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	BF01
Product key	BF1BJA
GTIN	4046356427838
Weight per piece (including packing)	46.7 g
Weight per piece (excluding packing)	45.2 g
Customs tariff number	85444290
Country of origin	PL

SAC-4P-M 8MS/ 1,0-PUR/M 8FSSH - Sensor/actuator cable



1574593

<https://www.phoenixcontact.com/us/products/1574593>

Technical data

Product properties

Product type	Sensor/actuator cable
Number of positions	4
No. of cable outlets	1
Shielded	yes
Coding	A

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Material specifications

Flammability rating according to UL 94	HB
Seal material	NBR
Material of grip body	TPU, hardly inflammable, self-extinguishing
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Material for screw connection	Zinc die-cast, nickel-plated

Electrical properties

Contact resistance	$\leq 5 \text{ m}\Omega$
Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	48 V AC
	60 V DC
Nominal current I_N	4 A

Signaling

Status display	No
Status display present	No

Connector

Connection 1

Type	Plug straight M8
Number of positions	4
Coding type	A
Number of positions	4

Connection 2

Type	Socket straight M8
Number of positions	4
	4


SAC-4P-M 8MS/ 1,0-PUR/M 8FSSH - Sensor/actuator cable



1574593

<https://www.phoenixcontact.com/us/products/1574593>

Cable/line

Cable length	1 m
PUR halogen-free black [PUR]	
Dimensional drawing	
Cable weight	31 kg/km
UL AWM Style	20549
Number of positions	4
Shielded	yes
Cable type	PUR halogen-free black [PUR]
Conductor structure signal line	32x 0.10 mm
AWG signal line	24
Conductor cross section	4x 0.25 mm ² (Signal line)
Wire diameter incl. insulation	1.17 mm ±0.02 mm (Signal line)
External cable diameter	4.7 mm ±0.15 mm
Outer sheath, material	PUR
External sheath, color	black-gray RAL 7021
Conductor material	Bare Cu litz wires
Material wire insulation	PP
Single wire, color	brown, white, blue, black
Thickness, insulation	≥ 0.21 mm (Core insulation) approx. 0.5 mm (Outer cable sheath)
Overall twist	4 wires, twisted
Optical shield covering	80 %
Max. conductor resistance	max. 78 Ω/km (at 20 °C)
Insulation resistance	≥ 100 GΩ*km (at 20 °C)
Nominal voltage, cable	≤ 300 V
Test voltage	≥ 3000 V
Smallest bending radius, fixed installation	24 mm
Smallest bending radius, movable installation	48 mm
Max. bending cycles	10000000
Halogen-free	in accordance with DIN VDE 0472 part 815
Flame resistance	in accordance with UL 758/1581 FT2 DIN EN 60332-2-2 (20 s)
Resistance to oil	in accordance with DIN EN 60811-2-1
Highly resistant to acids, alkaline solutions and solvents	

SAC-4P-M 8MS/ 1,0-PUR/M 8FSSH - Sensor/actuator cable



1574593

<https://www.phoenixcontact.com/us/products/1574593>

Other resistance	hydrolysis and microbe resistant
	partly UV-resistant in accordance with DIN EN ISO 4892-2-A
Special properties	Flexible cable conduit capable
	Silicone-free
	Free of substances which would hinder coating with paint or varnish
Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation)
	-25 °C ... 80 °C (Cable, flexible installation)

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65
	IP67
Ambient temperature (operation)	-25 °C ... 90 °C (Plug / socket)
	-25 °C ... 80 °C (cable, fixed installation)
	-5 °C ... 80 °C (Cable, flexible installation)

SAC-4P-M 8MS/ 1,0-PUR/M 8FSSH - Sensor/actuator cable




1574593

<https://www.phoenixcontact.com/us/products/1574593>


Drawings

Dimensional drawing



M8 x 1 male plug, straight version

Schematic diagram




Pin assignment M8 plug, 4-pos., view male side

SAC-4P-M 8MS/ 1,0-PUR/M 8FSSH - Sensor/actuator cable

1574593


<https://www.phoenixcontact.com/us/products/1574593>

Schematic diagram



Pin assignment M8 socket, 4-pos., view female side

Dimensional drawing



Socket M8 x 1, straight, shielded


SAC-4P-M 8MS/ 1,0-PUR/M 8FSSH - Sensor/actuator cable



1574593

<https://www.phoenixcontact.com/us/products/1574593>

Circuit diagram



SAC-4P-M 8MS/ 1,0-PUR/M 8FSSH - Sensor/actuator cable



1574593

<https://www.phoenixcontact.com/us/products/1574593>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1574593>



UL Listed

Approval ID: FILE E 221474

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	30 V	4 A	-	-



cUL Listed

Approval ID: FILE E 221474

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	30 V	4 A	-	-

cULus Listed

SAC-4P-M 8MS/ 1,0-PUR/M 8FSSH - Sensor/actuator cable



1574593

<https://www.phoenixcontact.com/us/products/1574593>

Classifications

ECLASS

ECLASS-11.0	27060311
ECLASS-12.0	27060311
ECLASS-13.0	27060311

ETIM

ETIM 8.0	EC001855
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SAC-4P-M 8MS/ 1,0-PUR/M 8FSSH - Sensor/actuator cable



1574593
<https://www.phoenixcontact.com/us/products/1574593>

Environmental product compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Phoenix Contact 2023 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com