




Product: [9180](#)

Audio Cable, #26-1pr, TC, O/A Foil, CM



### Product Description

Audio Cable, 110 Ohm, 26 AWG stranded (7x34) .018" TC conductors, Datalene® insulation, twisted pair, Beldfoil® shield (100% coverage), 26 AWG stranded TC drain wire, PVC jacket.

### Technical Specifications

#### Product Overview

Suitable Applications:	Low Voltage analog Signals (4-20mA, 0-10V, ...); Low Voltage Digital Control (24V, ...); Line Level audio; Computer Communication; Panel Wiring
------------------------	---

#### Construction Details

##### Conductor

Size	Stranding	Material
26	7x34	TC - Tinned Copper

##### Insulation

Material	Nom. Thickness	Nom. Insulation Diameter	Color Code	Notes
PE - Polyethylene (Foam)	0.015 in (0.38 mm)	0.049 in (1.2 mm)	Black & White	HDPE

##### Outer Shield

Shield Type	Material	Coverage
Tape	Bi-Laminate (Alum+Poly)	100%

##### Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.022 in (0.56 mm)	0.144 in

#### Electrical Characteristics

##### Electricals

Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Nom. Characteristic Impedance	Nom. Velocity of Prop.	Max. Current
37.3 Ohm/1000ft (122 Ohm/km)	13 pF/ft (43 pF/m)	26 pF/ft (85 pF/m)	110 Ohm	76%	1.9 Amps per Conductor at 25°C

##### Voltage

UL Voltage Rating
300 V RMS

#### Mechanical Characteristics

##### Temperature

UL Temperature	Operating
60°C	-40°C To +75°C

Max. Pull Tension:	10.5 lbs (4.76 kg)
Bulk Cable Weight:	10 lbs/1000ft (15 kg/km)

#### Standards and Compliance

Environmental Suitability:	Indoor - Riser, Indoor
Flammability / Reaction to Fire:	UL1685 FT4 Loading, IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	CMR
CEC / C(UL) Compliance:	CMG
European Directive Compliance:	EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Other Standard Compliance(s):	AES/EBU

## Product Notes

Notes:	For cross-connect use with 7891A (et al.) Digital Audio Snake Cables.
--------	---

## History

Update and Revision:	Revision Number: 0.442 Revision Date: 01-20-2023
----------------------	--

## Part Numbers

### Variants

Item #	Color	Putup Type	Length	UPC
9180 0601000	Chrome	Reel	1,000 ft	612825225089
9180 Z4B1000	Violet Z4B	Reel	1,000 ft	612825407386

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.