

Specification Sheet

Part Number: SNP10GHS0M4

Installation and removal can be five times faster than conventional clamps

.

Heat stabilized material is suitable for high temperature applications.

Completely reusable

.

Will not rust or corrode

.

Safety engineered.

No protruding band or cluster.

Can be installed with hose in place

.

One-hand installation for tight places.



Snapper Hose Clamp, 0.57 - 0.65" Bundle Diameter, PA66GF13, Black, 1000/pkg

Article Number	190-00043
----------------	-----------

Type	SNP10
------	-------

Color	Black (BK)
-------	------------

Quantity Per	bag
--------------	-----

Product Description	The Snapper Hose Clamp features a ratchet-style closure for reduced assembly time. It can be added after connection of the hose. Release by sliding the ratchet ends apart. Snappers can be used in under-hood applications and are stable in a wide variety of chemicals including salts, bases, alcohols, ethers, detergents, gasoline, lubricating oils and greases. They are manufactured in black PA66 glass filled, impact modified, heat stabilized material. Custom design and color options are available based upon application and volume requirements.
Short Description	Snapper Hose Clamp, 0.57 - 0.65" Bundle Diameter, PA66GF13, Black, 1000/pkg
Global Part Name	SNP10-PA66GF13-BK
Fixation Method	Plug-in mounting
Variant	Closed
Bundle Diameter Min (Imperial)	0.57
Bundle Diameter Min (Metric)	14.5
Bundle Diameter Max (Imperial)	0.65
Bundle Diameter Max (Metric)	16.6
Wall Thickness WT (Imperial)	.069
Wall Thickness WT (Metric)	1.717
Material	Polyamide 6.6 glass filled impact modified heat stabilized (PA66GF13%)

Material Shortcut	PA66GF13
Flammability	UL 94 HB
UV Resistant (Yes/No)	No
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)