

Specification Sheet

Part Number: 113-00061



Reinforcement ribs between the screw mount and cable tie head provide additional strength for added bundle stability and security.
Simple one piece design for quick and easy installation.
Secures with a screw or bolt.

1-Pc Cable Tie/Screw Mount, 8.5" Long, 0.2" Hole, 1.8" Max Bundle Dia, 50lb, PA66HS, Black, 1000/pkg

Article Number	113-00061
Type	T50MRX
Color	Black (BK)
Quantity Per	bag
Product Description	Screw Mount Cable Ties attach to existing holes using a screw or bolt to provide a fastening point to secure and route wire and cable bundles. Reinforced ribs between the screw mount and cable tie head provide additional strength for added bundle stability and security.
Short Description	1-Pc Cable Tie/Screw Mount, 8.5" Long, 0.2" Hole, 1.8" Max Bundle Dia, 50lb, PA66HS, Black, 1000/pkg
Global Part Name	T50MRX-PA66HS-BK

Minimum Tensile Strength (Imperial)	50.0
Minimum Tensile Strength (Metric)	225.0
Length L (Imperial)	8.0
Length L (Metric)	203.2
Fixation Method	Fixing hole
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.2
Width W (Metric)	4.7
Bundle Diameter Min (Imperial)	0.06
Bundle Diameter Min (Metric)	1.5
Bundle Diameter Max (Imperial)	1.77
Bundle Diameter Max (Metric)	45.0
Height H (Imperial)	.24

Height H (Metric) 6.0

Mounting Hole Diameter D (Imperial) 0.2

Mounting Hole Diameter D (Metric) 5.2 mm

Mounting Hole Diameter D Max (Metric) 5.2

Material Polyamide 6.6 heat stabilized (PA66HS)

Material Shortcut PA66HS

Flammability UL 94 V-2

UV Resistant (Yes/No) No

Operating Temperature -40°F to +257°F (-40°C to +125°C)

Reach Compliant (Article 33) No

ROHS Compliant Yes

Certification/Specification UL 62275

UL Recognized (US) Yes

UL Listed (US and Canada) Yes

UL Recognized (US and Canada) Yes

UL Listed (US)	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).