

Specification Sheet

Part Number: 170-03010



Treated polyester material contains a combustion inhibitor for use in applications where flame retardancy is required. Braided design allows sleeving to expand by 150% to accommodate variations in wire bundle and eases installation.

Braided Sleeving, Expandable, Flame Retardant, 1.25" Dia, PET, Black, 50 ft/reel

Article Number	170-03010
Type	BSPFR1140
Color	Black (BK)
Quantity Per	reel
Product Description	A flame retardant woven (threaded) polyester sleeving that is resistant to cuts and abrasion, and contains a combustion inhibitor allowing it to achieve a UL and CSA flame resistance rating of VW-1. Contains white tracer thread for easy identification.
Short Description	Braided Sleeving, Expandable, Flame Retardant, 1.25" Dia, PET, Black, 50 ft/reel
Global Part Name	BSPFR1140-PET-BK

Length L (Imperial)	50.0
---------------------	------

Length L (Metric)	15.2
-------------------	------

Bundle Diameter Min (Imperial)	0.75
--------------------------------	------

Bundle Diameter Min (Metric)	19.1
------------------------------	------

Bundle Diameter Max (Imperial)	1.75
--------------------------------	------

Bundle Diameter Max (Metric)	44.5
------------------------------	------

Diameter D (Imperial)	1.25
-----------------------	------

Diameter D (Metric)	31.8
---------------------	------

Nominal Diameter (Imperial)	1.25
-----------------------------	------

Nominal Diameter (Metric)	31.8
---------------------------	------

Material	Polyester (PET)
----------	-----------------

Material Shortcut	PET
-------------------	-----

Flammability	FMVSS 302 FAR 25 Mil-202 UL 224 VW-1
--------------	--------------------------------------

Halogen Free	Yes
--------------	-----

UV Resistant (Yes/No)	No
-----------------------	----

Operating Temperature	-94°F to +257°F (-70°C to +125°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL 94 VW-1
UL Recognized (US)	Yes
Package Quantity (Imperial)	50
Package Quantity (Metric)	15.24
Customs Number	5808100000

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).