

Specification Sheet

Part Number: CMFO4



Markers are pre-coiled so that they can be snapped into place over the cable without the use of adhesives.

Non-adhesive design means that the markers can be installed at any temperature or over dirty or oily surfaces.

Pre-printed text is protected by a thick layer of clear acrylic which provides UV protection and abrasion resistance.

Fiber Optic Cable Marker, Coiled, 4.0" x 4.0", VL, Orange, 25/pkg

Article Number	597-00042
Type	CMF
Color	White (WH)
Quantity Per	pack
Product Description	HellermannTyton's coiled markers are made from heavy duty vinyl and come pre-printed with a standard warning.
Short Description	Fiber Optic Cable Marker, Coiled, 4.0" x 4.0", VL, Orange, 25/pkg
Global Part Name	CMF-V-WH

Length L (Imperial)	5.0
Length L (Metric)	127.0
Width W (Imperial)	4.0
Width W (Metric)	101.6
Height H (Imperial)	3.0
Height H (Metric)	76.2
Outside Diameter Max (Imperial)	0.75
Outside Diameter Min (Metric)	12.7
Outside Diameter Min (Imperial)	0.5
Outside Diameter Max (Metric)	19.01
Material	Vinyl (V)
Material Shortcut	V
Halogen Free	No
UV Resistant (Yes/No)	No
Operating Temperature	-18°F to +200°F (-29°C to +93°C)

Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Package Quantity (Imperial)	25
Package Quantity (Metric)	25
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)