

Specification Sheet

Part Number: 151-02262



Clip can be installed by hand – no need for hardware or tools.
Design provides low insertion and high extraction force, for simple, secure performance.

Clip keeps bundle away from areas that could cause damage due to rubbing.

Standoff Bundling Clip, 1.97" Long, Panel Thickness 0.02 - 0.16", PA66HIRHS, Black, 1000/carton

Article Number

151-02262

Type

SOC13FTOVAL

Color

Black (BK)

Quantity Per

carton

Product Description

Bundling clips are designed to provide simple and easy methods of securing cable bundles, hoses, or pipes. They are fastened onto the tape bar using bundle or cable ties. The different fixing orientations allow tape clips to be used with a wide range of panel thicknesses and hole diameters. Standard bundling clips are available as well as standoff and stud mount versions.

Short Description

Standoff Bundling Clip, 1.97" Long, Panel Thickness 0.02 - 0.16", PA66HIRHS, Black, 1000/carton

Global Part Name	SOC13FTOVAL-PA66HIRHS-BK
------------------	--------------------------

Length L (Imperial)	1.97
---------------------	------

Length L (Metric)	50.0
-------------------	------

Offset Length (Imperial)	0.79
--------------------------	------

Offset Length (Metric)	20.0
------------------------	------

Fixation Method	Fir Tree for oval holes
-----------------	-------------------------

Panel Thickness Min (Imperial)	0.02
--------------------------------	------

Panel Thickness Max (Imperial)	0.16
--------------------------------	------

Panel Thickness Min (Metric)	0.6
------------------------------	-----

Panel Thickness Max (Metric)	4.0
------------------------------	-----

Mounting Hole Diameter D (Imperial)	0.25 x 0.5
-------------------------------------	------------

Mounting Hole Diameter D (Metric)	6.5 x 12.5 mm
-----------------------------------	---------------

Mounting Hole Diameter D Min (Imperial)	0.25
---	------

Mounting Hole Diameter D Max (Imperial)	0.5
---	-----

Mounting Hole Diameter D Max (Metric)	12.5
---------------------------------------	------

Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Shortcut	PA66HIRHS
Operating Temperature	-40°F to +230°F (-40°C to +110°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	1000
Package Quantity (Metric)	1000
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).