

Mini DisplayPort 1.2 to VGA Active Adapter Cable (M/M), 3 ft. (0.9 m)

MODEL NUMBER: **P586-003-VGA-V2**
Converts a Mini DisplayPort v1.2 video signal for display on a VGA monitor, projector or television.

Features

- Send High-Quality Mini DisplayPort v1.2 Video Signals to a VGA Display**
- Connects Mini DisplayPort (or Thunderbolt) computer to VGA-enabled monitor, projector or TV
 - Ideal for displaying video on large monitor or digital sign
 - Low-profile VGA connector fits neatly into available space; no jamming between wall and monitor or impeding neighboring connections
 - Mini DisplayPort and HD15 male connectors
 - No separate adapter required

- Vibrant, Superior Video Quality**
- Supports computer video resolutions up to 1920 x 1200
 - Supports HD video resolutions up to 1920 x 1080 (1080p)
 - Converts Single-Mode and Dual-Mode (DP++) Mini DisplayPort output
 - Perfect for use with graphics cards, such as AMD Eyefinity, that don't output DP++ signals

- Superior Materials for Superior Performance**
- Double shielding with foil and braid for maximum EMI/RFI protection
 - Nickel-plated connectors with gold-plated contacts for excellent conductivity
 - Integral strain relief for long life

Specifications

OVERVIEW	
UPC Code	037332191847
Product Type	Active Cable
Technology	VGA/SVGA; DisplayPort
Cable Type	Active
VIDEO	
Max Supported Video Resolution	1920 x 1200 (1080p)
HDR Support	No
PHYSICAL	
Color	Black
Material of Construction	ABS, PVC

- Highlights**
- Active adapter cable for use with any Mini Displayport (or Thunderbolt) port
 - Low-profile VGA connector fits neatly into available space; no jamming between wall and monitor or impeding neighboring connections
 - Supports computer video resolution up to 1920 x 1200
 - Supports HD video resolution up to 1920 x 1080 (1080p)
 - No separate adapter required
 - Nickel-plated connectors with gold-plated contacts

- Package Includes**
- P586-003-VGA-V2 Mini DisplayPort 1.2 to VGA Active Adapter Cable, 3 ft.

Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	5.0 +/- 15mm
Wire Gauge (AWG)	32
Cable Length (ft.)	3
Cable Length (m)	0.91
Cable Length (in.)	36
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.15
Shipping Weight (kg)	0.07
Unit Dimensions (hwd / in.)	9.000 x 7.000 x 0.500
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	5° to 122°F (-15° to 50°C)
Operating Humidity Range	0% to 85%, Non-Condensing
Storage Humidity Range	0% to 85%, Non-Condensing
CONNECTIONS	
Side A - Connector 1	MINI DISPLAYPORT (MALE)
Side B - Connector 1	HD15 (MALE)
Connector Plating	Nickel
Contact Plating	Gold
FEATURES & SPECIFICATIONS	
IP68 Rated	No
IP20 Rated	No
Displayport Specification	1.2
STANDARDS & COMPLIANCE	
Product Compliance	CE (Europe); FCC (USA); REACH; RoHS; Trade Agreements Act (TAA); UKCA; WEEE
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty



1000 Eaton Boulevard
Cleveland, OH 44122
United States

Product Warranty Period (U.S. & Canada)	3-year limited warranty
---	-------------------------



© 2023 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.