

PDU Power Cord, C13 to C14 - 10A, 250V, 18 AWG, 2 ft. (0.61 m), Black, 5-Pack

MODEL NUMBER: P004-002-5



Computer power extension cords connect 2 devices with C13/C14 power connectors or extend your existing power connection by 2 ft.

Features

C14-to-C13 Power Cables Connect Computers, Printers, Servers and Other Equipment This package of five IEC-320-C14 to IEC-320-C13 cables is designed for small data center, office workstation and other lower-amp applications. These C14 male to C13 female cords can be used to power computers, servers and monitors; attach routers and drives to a UPS system or PDU; or extend existing connections up to 2-ft. (0.61 m). The 2-ft. (0.61 m) length helps reduce cable clutter and minimize the risk of tripping.

Highlights

- Recommended for powering computers, printers and other essential peripherals
- Add 2-ft. (0.61 m) to your existing connection to provide more flexibility in placing devices
- C13-to-C14 PDU-style extension cords are ideal replacements for worn-out or missing cable

Applications

- Connect devices like computers, servers and routers to a PDU up to 2-ft. (0.61 m) away in your data center
- Extend existing power connections up to 2-ft. (0.61 m) to more easily place devices or reach a power source near your workstation
- Provide high-quality replacements for worn-out or missing power cords

Package Includes

- (5) C14 Male to C13 Female Power Cables, 2-ft. (0.61 m), Black

Specifications

OVERVIEW	
UPC Code	037332142863
Device Compatibility	Computer; Monitor/HDTV; Printer; Server; UPS; PDU
Country/Region	Global
INPUT	
Maximum Input Amps	10
Voltage Compatibility (VAC)	100-250
PHYSICAL	
Plug Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC

Cable Jacket Rating	FT2
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	7.7mm
Number of Conductors	3
Wire Gauge (AWG)	18
Wire Gauge (OD - mm ²)	0.82
Cable Length (ft.)	2
Cable Length (m)	0.61
Shipping Dimensions (hwd / in.)	14.17 x 11.80 x 0.50
Shipping Dimensions (hwd / cm)	35.99 x 29.97 x 1.27
Shipping Weight (lbs.)	1.10
Shipping Weight (kg)	0.50
ENVIRONMENTAL	
Operating Temperature Range	-4° to 140°F (-20° to 60°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Operating Humidity Range	20% to 80% RH
Storage Humidity Range	20% to 80% RH
CONNECTIONS	
Side A - Connector 1	IEC-320-C14
Side B - Connector 1	IEC-320-C13
FEATURES & SPECIFICATIONS	
Antibacterial	No
Angled Plug	No
High Voltage	Yes
Locking Plug	No
Coiled Power Cord	No
STANDARDS & COMPLIANCE	
Product Certifications	CSA (Canada); cUL Listed; UL Listed
Product Compliance	RoHS; REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty



1000 Eaton Boulevard
Cleveland, OH 44122
United States



© 2023 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.