

Specification Sheet

Part Number: 156-02624



One-piece ratchet closure allows for easy installation during pre- or final assembly.

Easy release feature simplifies quick adjustments and maintenance.

Impact modified, heat and UV stabilized PA66 provides long-term durability, indoors and out.

3M™ VHB™ adhesive on base creates an incredible bond with mounting surface.

Adhesive Mount Ratchet Clamp, 0.24 - 0.54" Bundle Dia, MB5A, PA66HIRHSUV, Black, 250/ctn

Article Number	156-02624
----------------	-----------

Type	IRCAMB5A
------	----------

Color	Black (BK)
-------	------------

Quantity Per	bag
--------------	-----

Product Description	The Inline Ratchet P-Clamp family offers versatility when managing wires, cables and hoses. Built-in attachments include round and oval for trees and adhesive mounts, so no additional hardware is needed for securing to a hole or panel. The robust design and durable materials make it ideal for heavy duty applications, both indoors and out. The adjustable clamp can be closed by hand to the desired diameter. The release feature allows easy and nondestructive removal of cables simply by using a flat-head screwdriver. In this way, the clamp can be reused or serviced without removing it from the mounting surface.
---------------------	--

Short Description	Adhesive Mount Ratchet Clamp, 0.24 - 0.54" Bundle Dia, MB5A, PA66HIRHSUV, Black, 250/ctn
Global Part Name	IRCAMB5A-PA66HIRHSUV-BK
Minimum Tensile Strength (Imperial)	100.0
Minimum Tensile Strength (Metric)	445.0
Length L (Imperial)	1.37
Length L (Metric)	34.8
Fixation Method	Adhesive
Width W (Imperial)	1.37
Width W (Metric)	34.9
Bundle Diameter Min (Imperial)	0.24
Bundle Diameter Min (Metric)	6.10
Bundle Diameter Max (Imperial)	0.54
Bundle Diameter Max (Metric)	13.72
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)

Material Shortcut	PA66HIRHSUV
Adhesive	Acrylic
Flammability	UL 94 HB
UV Resistant (Yes/No)	Yes
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Package Quantity (Imperial)	250
Package Quantity (Metric)	250
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).