








RoHS



P.C.B Layout(Pattern side)



规格说明:Specifications

电气特性:Electrical

1. 额定电流:Current Rating
1.5A/contact terminal
 2. 额定电压:Voltage Rating
30V DC
 3. 接触阻抗:Contact Resistance
50 milliohms Max
 4. 耐电压:Dielectric Withstanding Voltage
AC 500V/1MINUTE.
 5. 绝缘阻抗:Insulation Resistance
1000MEGA Ohms Min
- 物理性能:Mechanical
1. 插拔力:Cnnector Mate and Unmate Force
Insertion force:35N(3.57kgf)MAX
Extraction force:10-35N(1.02-3.57kgf)Min
- 端子保持力:Terminal Retenion
1.0kgf(MIN)
- 耐久性:Durability
3000cycles.EXTRACTLON FORCE:
10-35N(1.02-3.57kgf)

③	Terminal		4	Copper Alloy	Silvering
②	Shell		1	SPCC	Ni Plating
①	Base		1	PBT	White
NO.	Name	Number	Qty	Material	Remarks

YUANDI®  Yuandi Electronics Co,Ltd

design		date		name	USB CONNECTOR
Review		date			
Approved		date			
number:				model	AM90-01-T1-W

modify	Review	Approved	Tolerance not specified	Proportion	1:1	unit	mm	gape number		A4	
--------	--------	----------	-------------------------	------------	-----	------	----	-------------	--	----	---