

Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought







TE Part #2149966-1
Mini-SAS HD Cages




TE Part #3-1462039-0
IM23TS=IM RELAY 50mW 5V




TE Part #2205067-3
CA MICRO-MATCH MOW-MOW 18POS




TE Part #826467-4
4P MOD II SHROUDED HEADER, ST 18POS




TE Part #926476-6
MOD 4 HSG




TE Part #2-6609940-0
PM0SXDHXB=C3334



TE Part #1483351-1
MICRO-MATCH LEAD 06P 100MM



TE Part #1483356-1
MICRO-MATCH LEAD 16P 100MM



TE Part #1483358-1
MICRO-MATCH LEAD 20P 100MM

Documents

Product Drawings

MICRO-MATCH LEAD 18P 100MM

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1483357-1_A_c-1483357-1-a.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1483357-1_A_c-1483357-1-a.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1483357-1_A_c-1483357-1-a.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.