



Recommended PCB Layout ±0.05

Specifications:

规格:

Voltage rating:30V AC/DC

额定电压: 30V AC/DC

Current rating:0.3A AC/DC

额定电流: 0.3A AC/DC

Withstanding voltage:100V AC/minute

耐受电压: 100V AC/分钟

Temperature range:-35°C-+85°C

温度范围: -35°C-+85°C

Insulation resistance:50MΩ min

绝缘电阻: 50MΩ Min

Contact resistance:90mΩ Max

接触电阻: 90mΩ Max

X0408 W V S - XX X - LP V01

① ② ③ ④ ⑤ ⑥ ⑦ ⑧

1.Series No

2.Category:W-Wafer

3.Welding Board Angle:V-Stright 180°

4.Welding Way:S-SMT

5.Row No.Pin No:XX-10~100P

6.Height:A=1.14mm

7.Material:LP-LCP UL94V-0 Black

8.Plating:V01-Gold Flash

Poles	Dimensions(mm)		
	A	B	C
10	3.52	1.60	1.00
12	3.92	2.00	
20	5.52	3.60	
24	6.32	4.40	1.20
30	7.52	5.60	1.50
34	8.32	6.40	2.30
40	9.52	7.60	3.20
44	10.32	8.40	
50	11.52	9.60	
60	13.52	11.60	
70	15.52	13.60	
80	17.52	15.60	
90	19.52	17.60	
100	21.52	19.60	

X0408WVS-XXX-LPV01	LCP	Phosphor Bronze	X0408F
PART NO	Material	Material(Pin)	Suitable XKB Female

DSND	SCALE: N/A	MODEL TYPE: 0.4mm BTB Connector
DWN	VIEW:	PART NO.: X0408WVS-XXX-LPV01
CHKD	UNIT: mm/in	DWG NO.: X-X0408WVS-XXX-LPV01
APPD	SIZE: A4	



XKB INDUSTRIAL PRECISION CO., LIMITED

WEIGHT	SHEET	REVISION
	1/1	A0

广东星坤科技股份有限公司

审核	日期
签署	日期

文件工程章

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
					ANGULAR ±5°
					L ≤ 4 ±0.2
					4 < L ≤ 16 ±0.3
					16 < L ≤ 63 ±0.4
					L > 63 ±0.5